

3M™ H-700 Series Hard Hat



Ultimate Comfort Tough Performance

Experience Extended Comfort with the 3M H-700 Series Hard Hat

The 3M™ H-700 Series Hard Hat is engineered to help provide extended comfort, head protection, balance and stability. The lightweight H-700 series features a unique top of hat design with a short brim in both a vented and non-vented version. A 4-point ratchet or pinlock suspension system with height adjustment delivers the balance and stability you need in demanding work environments.



Solutions for Head and Face Protection



3M™ H-700 Series Hard Hat is comfortable, tough and lightweight. Designed with a low profile for stability and balance, the H-700 series helps provide ultimate comfort and protection from small falling objects striking the top of the hard hat. These hard hats feature accessory slots to accommodate 3M's cap-mounted earmuffs, headgear, faceshields and welding helmets. The H-700 series hard hat (non-vented) meets the requirements of ANSI/ISEA Z89.1-2009 Type I, Class C, G and E. The H-700 vented hard hat meets the requirements of ANSI/ISEA Z89.1 Type I, Class C.

The 3M H-700 Series Hard Hat Offers:

- Comfortable, 4-point pinlock or ratchet suspension with height adjustment
- Replaceable brow pad
- Vented hard hat option
- Customized logo options
- ANSI/ISEA compliant when worn in the forward and reverse donning positions
- Short brim for better upward visibility
- Slots for accessory attachment
- Optional 6-point strap available

H-700 Series Hard Hat Applications May Include:

- Heavy and Light Industrial
- Construction Work
- Oil and Gas
- Road Construction
- Forestry
- Mining

Part Number	Description (Ship Qty. – 20 ea/cs)	Color	4-Point Suspension	UPC
H-701P	3M™ Hard Hat H-701P	White	Pinlock	100 78371 64187 7
H-702P	3M™ Hard Hat H-702P	Yellow	Pinlock	100 78371 64188 4
H-703P	3M™ Hard Hat H-703P	Blue	Pinlock	100 78371 64189 1
H-704P	3M™ Hard Hat H-704P	Green	Pinlock	100 78371 64190 7
H-705P	3M™ Hard Hat H-705P	Red	Pinlock	100 78371 64191 4
H-706P	3M™ Hard Hat H-706P	Orange	Pinlock	100 78371 64192 1
H-707P	3M™ Hard Hat H-707P	Bright Orange	Pinlock	100 78371 64193 8
H-708P	3M™ Hard Hat H-708P	Gray	Pinlock	100 78371 64194 5
H-709P	3M™ Hard Hat H-709P	Bright Yellow	Pinlock	100 78371 64195 2
H-710P	3M™ Hard Hat H-710P	Navy Blue	Pinlock	100 78371 64196 9
H-701R	3M™ Hard Hat H-701R	White	Ratchet	100 78371 64197 6
H-702R	3M™ Hard Hat H-702R	Yellow	Ratchet	100 78371 64198 3
H-703R	3M™ Hard Hat H-703R	Blue	Ratchet	100 78371 64199 0
H-704R	3M™ Hard Hat H-704R	Green	Ratchet	100 78371 64200 3
H-705R	3M™ Hard Hat H-705R	Red	Ratchet	100 78371 64201 0
H-706R	3M™ Hard Hat H-706R	Orange	Ratchet	100 78371 64202 7
H-707R	3M™ Hard Hat H-707R	Bright Orange	Ratchet	100 78371 64203 4
H-708R	3M™ Hard Hat H-708R	Gray	Ratchet	100 78371 64204 1
H-709R	3M™ Hard Hat H-709R	Bright Yellow	Ratchet	100 78371 64205 8
H-710R	3M™ Hard Hat H-710R	Navy Blue	Ratchet	100 78371 64206 5
H-701V	3M™ Vented Hard Hat H-701V	White	Ratchet	100 78371 64207 2
H-702V	3M™ Vented Hard Hat H-702V	Yellow	Ratchet	100 78371 64208 9
H-703V	3M™ Vented Hard Hat H-703V	Blue	Ratchet	100 78371 64209 6
H-704V	3M™ Vented Hard Hat H-704V	Green	Ratchet	100 78371 64210 2
H-700-RS4	3M™ H-700 Series Hard Hat Suspension Replacement	—	Ratchet Standard	100 78371 64211 9
H-700-PS4	3M™ H-700 Series Hard Hat Suspension Replacement	—	Pinlock Standard	100 78371 64212 6
H-700-BP	3M™ Hard Hat Replacement Brow Pad H-700-BP	—	—	100 78371 65491 4
H-700-S6	3M™ Hard Hat Suspension 6-Point Strap H-700 Series	—	—	100 78371 65492 1

Colors Available:



Accessories Available:



For More Information in the U.S.

Technical Assistance: 1-800-243-4630 Customer Care Center: 1-800-328-1667 Internet: 3M.com/PPESafety



3M Occupational Health and Environmental Safety Division
3M Center
St. Paul, MN 55144-1000

3M is a trademark of 3M Company, used under license in Canada. Please recycle. Printed in U.S.A.
© 3M 2011. All rights reserved. 70-0715-7450-6

Made in U.S.A. with Globally Sourced Materials.

WARNING

3M™ H-700 Series Hard Hat provides limited protection

only. Misuse or failure to follow warnings and User Instructions may result in serious personal injury or death. For proper use, see supervisor, User Instructions, or call 3M Occupational Health and Environmental Safety Division (OH&ESD) Technical Assistance in the USA at 1-800-243-4630. In Canada, call 1-800-267-4414.