



© Copyright 1998. All rights reserved.  
Black Box Corporation.

# BLACK BOX<sup>®</sup>

The World's Source for Connectivity<sup>SM</sup>

## Indoor/Outdoor Utility Cords

*These Utility Cords are available in the lengths you need and are guaranteed for life.*

### Key Features

Utility Cords

► **Premium-quality 3-wire indoor/outdoor extension cords feature heavy-duty vinyl construction.**

► **Grounded cords feature three rugged outlets.**

► **Designed for industrial usage and long life.**

Ground-Fault Interrupter Cord

► **Heavy-duty Cord features a male ground-fault interrupter and a triple, female outlet.**

► **Built-in circuit breaker provides double protection.**

► **Rated for 125 volts.**

### For these and other components...

*Call our expert Technical Support Staff for all your Tools/Racks needs. They'll help you find the best equipment for your application.*

### Technically Speaking

**T**hese all-weather extension cords are rated for 125 volts. They are guaranteed for life, and they're available in 15', 25', 50', and 100' lengths.

EPWR30, 32, 34, 36  
These cords are 14 gauge with 3 wires. They're grounded and designed for a single outlet. They have a 0.39-inch diameter and an orange vinyl jacket.

EPWR40, 42, 44, 46  
These cords are 14 gauge with 3 wires. They're grounded and designed for a triple outlet. They have a 0.39-inch diameter and an orange vinyl jacket. They are UL<sup>®</sup> listed.

EPWR60, 62, 64, 66  
These cords are 14 gauge with 3 wires. They're grounded and designed for a triple outlet. They have a 0.39-inch diameter and a black vinyl jacket.

EPWR50, 52, 54, 56

These cords are 12 gauge with 3 wires. They're grounded and designed for a single outlet. They have a 0.48-inch diameter and a blue vinyl jacket. And these cords are flexible down to -58° F.

EPL115

The Ground-Fault Interrupter Cord features a male ground-fault interrupter and a female triple outlet with a built-in circuit breaker for double protection. And it's UL<sup>®</sup> listed.

## Ordering Information

*This information will help you place your order quickly.*

PRODUCT NAME	ORDER CODE
Single Outlet 14/3, Grounded, Orange, Heavy-Duty	
15-ft.....	EPWR30
25-ft.....	EPWR32
50-ft.....	EPWR34
100-ft.....	EPWR36
Triple Outlet 14/3, Grounded, Orange, Heavy-Duty	
15-ft.....	EPWR40
25-ft.....	EPWR42
50-ft.....	EPWR44
100-ft.....	EPWR46
Triple Outlet 14/3, Grounded, Black, Heavy-Duty	
15-ft.....	EPWR60
25-ft.....	EPWR62
50-ft.....	EPWR64
100-ft.....	EPWR66
Triple Outlet 12/3, Grounded, Blue, XX Heavy-Duty	
15-ft.....	EPWR50
25-ft.....	EPWR52
50-ft.....	EPWR54
100-ft.....	EPWR56
Ground-Fault Interrupter Cord, 2-ft .....	EPL115