



HAMMOND MANUFACTURING

1182R117
50/60Hz VA:1000

PRI: 2x 117V BLK-WHT, BRN-ORN
SEC: 2x 117V @ 4.30A RED-BLU, GRY-YEL

1A1000A000C117117

MADE IN CANADA DATE PB

RoHS Compliant

CE, UL, and other certification marks.

SUPPLIED WITH: TWO 0.093" T X 4.75" OD RUBBER WASHERS.
ONE 16GA X 4.30" OD STEEL MOUNTING WASHER.
ONE 3/8-16 BOLT 3.50" LONG WITH A LOCK WASHER AND 3/8-16 HEX NUT.

ELECTRICAL DATA:		
TESTS	CONDITIONS	ACCEPTANCE CRITERIA
Sec. N.L.V	@ 117V, 60Hz	
	BLK & BRN to WHT & ORN	
OR	@ 234V, 50Hz	
	BLK to ORN (Connect BRN & WHT)	
	RED - BLU	120.50 V ±2%
	GRY - YEL	120.50 V ±2%
POLARITY	BLK, BRN, RED and GRY.	ADDITIVE
DCR	BLK - WHT	0.350 Ohms ±20%
IN OHMS	BRN - ORN	0.350 Ohms ±20%
	RED - BLU	0.380 Ohms ±20%
	GRY - YEL	0.380 Ohms ±20%
HI POT	PRIMARY - SECONDARY	4000V, 60Hz, 1 SEC
	PRIMARY - PRIMARY	600V, 60Hz, 1 SEC
	SECONDARY - SECONDARY	600V, 60Hz, 1 SEC

PROPERTY AND COPYRIGHT NOTICE			
THIS DRAWING AND THE INFORMATION IT CONVEYS ARE THE PROPERTY OF HAMMOND MANUFACTURING. IT MAY NOT BE REPRODUCED, TRANSMITTED OR USED IN ANY MANNER WHATSOEVER WITHOUT THE WRITTEN PERMISSION OF HAMMOND MANUFACTURING.			
REV	NOTES	BY	DATE
1	UPDATED THE HARDWARE, WAS 1/4-20 X 3.5" LONG.	GG	15/04/14
		HAMMOND MANUFACTURING ELECTRONIC DIVISION 52 RANKIN PLACE, WATERLOO, ONTARIO, N2J 3Z5 PHONE: 519.886.6181 FAX: 519.886.9540	
TOROID POWER TRANSFORMER			
DRAWN G. GRAY		DATE 21/03/2014	NUMBER 1182R117
APPROVED		DATE	