

## R7240-2GD3-L

### SAP provides 2.5X longer graphics card lifespan

#### **ASUS Exclusive Innovations**

## Super Alloy Power Enhanced durability and cooling

Exclusively-formulated alloy components boost performance by reducing power loss, enhancing durability, and achieving cooler operation. Choke concrete cores eliminate buzzing sound under full load while capacitors assure a 50,000-hour lifespan: equivalent to 2.5 times longer than traditional capacitors.



# Dust-Proof Fan25% longer graphics card lifespan

Unique fan design dissipates heat efficiently while extending a graphic card's lifespan by 25%\* through increased dust and particle resistance.





# ASUS GPU Tweak with online streaming Real-time and intuitive tweaking

GPU Tweak helps you modify clock speeds, voltages, fan performance and more, all via an intuitive interface. What's more, a simple online-streaming function lets you share gameplay live – so people can watch as you play!





#### **ASUS Exclusive Innovations**

#### **Graphics GPU Feature**



#### Gigantic 2GB DDR3 **Memory:**

On-board memory for the best gaming experience & the best resolution



#### ● AMD Radeon™ R7 240



#### Low Profile Design:

Low profile graphics cards for HTPC and multimedia PCs support smooth 1280 x 1024 gaming and Blu-ray 3D. Brackets bundled for fast setup!



#### • AMD App Acceleration:

Speeds up daily applications such as web browsing and video playback. Also the first to provide support for both OpenCL, C++ AMP, and DirectCompute 11.




#### AMD PowerTune technology:

Intelligent power monitoring in the AMD Radeon™ graphics to enable higher clock speeds and better performance in your favorite games.



#### I/O Specifications





#### AMD ZeroCore Power technology:

Allows your AMD Radeon™ graphic to consume virtually no power when in idle state. It even shuts down additional GPUs in AMD CrossFire™ technology mode to consume less when they're not in use.



#### Microsoft DirectX 11.2 API

Brings new levels of visual realism to gaming on the PC and get top-notch performance.



#### Microsoft® Windows 8.1 compatible

Gives you access to advanced computing experiences with the latest operating system so you get more done with your PC



### **Hardware Specification**

Model	R7240-2GD3-L
Graphics Engine	AMD Radeon™ R7 240
Bus Standard	PCI Express® 3.0
OpenGL	OpenGL® 4.3
Video Memory	2048MB DDR3
GPU Clock	780 MHz
Stream Processor	320
Memory Clock	900 MHz(1800 MHz DDR3)
Memory Interface	128 bit
DVI Max. Resolution	1920*1200
DVI Output	1x Single-link DVI-D
HDMI Output	1x Native HDMI
HDCP compliant	YES
Software Bundled	ASUS GPU Tweak & Driver
Dimension	15.9 x 11.1 x 2 cm

<sup>•</sup>Specifications are subject to change without notice.
•PCB color and bundled software versions are change without notice.
•Brand and product names mentioned are trademarks of their respective company.