

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

54548-1370

Status:

Active

Overview:

FFC-FPC (SMT)

Description:

0.50mm Pitch Easy-On™ Type FFC/FPC Connector, 1.20mm Height, Right Angle, SMT, ZIF, Bottom Contact Style, 13 Circuits, Lead-Free

Documents:

3D Model

Drawing (PDF)

Product Specification PS-54548-038 (PDF)

Packaging Specification SPK-54548-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Overview

Product Name

UPC

FFC/FPC Connectors

54548

FFC-FPC (SMT)

Easy-On™

822348128914

Physical

Circuits (Loaded)

Color - Resin

Contact Position

Durability (mating cycles max)

Entry Angle

Mated Height

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PCB Locator

PCB Retention

Packaging Type

Pitch - Mating Interface

Plating min - Mating

Plating min - Termination

Polarized to PCB

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

Wire/Cable Type

13

Black, Natural

Bottom

20

90° Angle

1.20mm

Phosphor Bronze

Tin-Bismuth

Tin-Bismuth

High Temperature Thermoplastic

75.702/mg

1

Right Angle

No

Yes

Embossed Tape on Reel

0.50mm

1.016µm

1.016µm

Yes

No

N/A

-20°C to +85°C

Surface Mount

FFC/FPC

Electrical

Current - Maximum per Contact

Voltage - Maximum

0.5A


50V

Material Info

Reference - Drawing Numbers

Packaging Specification

SPK-54548-001



EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

54548Series

Product Specification

Sales Drawing

PS-54548-038, RPS-54548-079, RPS-54548-080,
RPS-54548-082, RPS-54548-084, RPS-54548-086,
RPS-54548-090, RPS-54548-098, RPS-54548-100
SD-54548-037, SD-54548-038

This document was generated on 03/26/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION