

## General Information

Extended Product Type:	463RU6W
Product ID:	2CMA167396R1000
EAN:	7392696673969
Catalog Description:	Socket-outlet, panel mounting, 6h, 63A, IP67, unified flange, straight, 3P+N+E
Long Description:	Socket-outlet, panel mounting, earthing sleeve position 6h, rated current 63A, IP67 watertight, unified flange, straight, 3-poles+neutral+earth, frequency 50-60 Hz, color code Red

## Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Socket Outlets for Panel Mounting

## Ordering

EAN:	7392696673969
Minimum Order Quantity:	1 piece
Country of Origin:	Czech Republic (CZ)

## Dimensions

Product Net Width:	107 mm
Product Net Height:	137 mm
Product Net Length:	111 mm
Product Net Depth:	137 mm
Product Net Weight:	0.76 kg

## Container Information

Package Level 1 Width:	117 mm
Package Level 1 Length:	141 mm
Package Level 1 Height:	117 mm
Package Level 1 Gross Weight:	0.76 kg
Package Level 1 EAN:	7392696673969
Package Level 1 Units:	1 piece

## Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-03-01
--------------	--

## Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	<a href="#">2CMC700005D0001;</a>
Environmental Information:	<a href="#">2CMC700001D0002;</a>
RoHS Information:	<a href="#">2CMC700047D0001;</a>

## Additional Information

Cable Cross-Section:	6 ... 25 mm <sup>2</sup>
Color:	Red
Degree of Protection:	IP67
Enclosure Material:	Thermoplastic polyester (PBT)
Frequency (f):	50 Hz 60 Hz
Function:	Socket outlet, panel mounting, unified flange, straight
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#463RU6W
Mounting Type:	unified flange, straight
Number of Poles:	5
Object Classification Code:	2CMT005069
Product Main Type:	RU
Product Name:	Industrial Socket Outlet Panel Mounting
Protection Type:	Watertight
Rated Current (I <sub>n</sub> ):	63 A
Rated Voltage (U <sub>r</sub> ):	346 ... 415 V
RoHS Date:	2009-01
Standards:	IEC 60309-1,-2
Suitable For:	Socket Outlets for Panel Mounting
Suitable for Product Class:	Industrial Plugs and Sockets

## Classifications

---

E-nummer: 2416752  
UNSPSC: 39120000

---

