



▲ **Front Mesh Cover for High Cooling Performance**

The front mesh bay cover provides cool air into the system while dust filters prevent dust from entering.



▲ **Supports up to 7 System Fans**

Up to 7 system fans are installed to expel hot air effectively from the case.



▲ **Zalman`s Powerful HDD Cooling Solution**

Interactive Cooling System : Hot air generated from HDD is expelled through both sides. Cooling Performance is maximized for HDD cooling, and the overall PC exhaust is increased.



▲ **Top Air Vent Exhaust/Tuning**

For user convenience, Top air vents expel exhaustive air from the top cooling fan. In addition, translucent acryl vents are effective for tuning.




▲ **Side-Panel Acryl Tuning**

Dynamic Side Acryl Tuning is provided for users to view the interior of gaming system.



▲ **Supports 4 USB 2.0**

I/O module provides 4 USB 2.0 ports for user convenience and expandability.



▲ **Dust Filters for Front and Bottom of System and PSU**

Dust filters in the front and bottom mesh covers prevent dust from entering the system and keep the internal components dust-free.



▲ **Additional Card Holder Provided**

When installing VGA Card and PCI Slot, the bracket can be used permanently.



▲ **Supports Bottom PSU Installation and Aperture for Cable Management**

Z11 Plus supports bottom PSU installation and provides an aperture for cable management to make better use of interior space.



▲ **Black Interior Coating**

The interior of chassis is coated black to provide a sense of unity and elegant design.



▲ **Anti-Vibration Rubber Stand**

Anti-Vibration Rubber prevents noise and also keeps the system safe from water or other liquid.




▲ **Tool Free HDD Installation with Anti-Vibration Rubber**

The server-type Tool-Free HDD Mount Trays allow easy HDD installation/removal and maintenance.



▲ **Spacious Interior for 290mm Card Installation**


The interior has been designed to be spacious for easy installation and maintenance of various components.



▲ **Supports Solid-State Drive (SSD)**

Space is provided on the back of M/B plate for installing 2.5" HDD/SSD.

※ Use the bracket located on the 5.25" bay.



▲ **Separate Apertures for Convenient CPU Cooler Installation**

Separate apertures for CPU cooler are provided for convenient CPU cooler installation without having to remove motherboard from case.



▲ **3-in-1 Bracket Provided**

3IN1 Adapter Tray is provided for installing FDD / 3.5"



▲ **Rear Tube Apertures for Liquid Cooling Systems**

Tube apertures are provided at the rear of the case for convenient water

## COMPONENTS



## SPECIFICATIONS

Enclosure Type	ATX Mid Tower	
Dimensions	260(W) x 498(H) x 525(D)mm	
Weight	7.3kg	
Material	Plastic, Steel	
Motherboard Compatibility	Standard ATX / Micro ATX	
Power Supply Compatibility	Standard ATX / ATX12V	
VGA Compatibility	Full Size (up to 290mm)	
Expansion Slot	7	
Drive Bays	5.25"	External Bay x 4
	3.5"	External Bay x 1, Internal Bay x 5
	5.25"/3.5"/2.5"	1 (3in-1)
Cooling Components	Front	1 x 120mm Blue LED Fan (120mm / 140mm)
	Top	2 x 120mm Fan (Optional)
	Rear	1 x 120mm Fan (Standard)
	Side	2 x 80mm Fan
	Bottom	120mm/140mm Fan Vent x 1 (Fan optional)
I/O Ports	Mic x 1, Headphones x 1, USB 2.0 x 4	
Color	Black	