

# "ATX MINI TOWER PC CASE"

## Z5 Series

### Sales Guide

2012. 07.

# Z5 Series

## With Zalman Cooling Solution

- Up to 5 system fans
- Bottom PSU installation
- Powerful cooling

## Design & Function

- Black coating
- Simplicity
- Convenient top interface
- Connect to smartphone & external hard drive
- Tube apertures for liquid cooling systems
- Front/Bottom dust filter
- View through side acryl


## Inner Structure

- 330mm high efficiency VGA card installation space
- Safe edge molding
- Tool free HDD installation system
- Anti-vibration and sound absorption rubber
- Spacious interior
- 3in1 Bracket provided
- 2.5" HDD/SSD installation on the case bottom
- CPU cooler hole provided for easy cooler installation



# UP To 5 System Fans

Up to 5 fans can be mounted with standard-equipped 120mm front LED fan and back 120mm fan.  
(extra 120mm LED fan standard-equipped on Z5 Plus)






## Bottom PSU Installation

Supports bottom PSU installation for effective cooling of PSU and inner space of case



# Powerful Cooling

Aerodynamically designed front/top vents provide cool air into the system.



# Black Coating

Luxurious interior with black coating finishing touch.





# Convenient Top Interface

USB ports, audio socket, power and rest buttons set on the top for user convenience.  
(USB 3.0 & fan controller available only on Z5 Plus)





## Connect To Smartphone & External Hard Drive

Place smart phone, external hard drive on the stand next to the USB port for convenient charging and connection.





# Tube Apertures for Liquid Cooling Systems

Tube apertures are provided at the rear of the case for convenient water cooling set-up and maintenance.







## Bottom Dust Filter

Dust filters on the bottom side prevent dust from entering.



## View through Side Acryl (Z5 Plus Only)

Side Acryl Tuning is provided for users to view the interior of gaming system.





**330mm**

## High Quality VGA Card

Without the side guide 330mm high performance VGA card can be installed.



# Safe Edge Molding

Safe edge molding for safer installing environment.





## Tool Free HDD Installation

Easily install HDD without any tool .



# Anti-vibration & Sound Absorption Rubber

Anti-slip rubber at the bottom of the case and the PSU helps to eliminate vibration sound .





## **Spacious Interior**

Provides spacious interior with 7 PCI extension slots.



## 3 in 1 Bracket

3in1 Adapter Tray is provided for installing FDD / 3.5" HDD / 2.5" HDD/SSD.



# Additional 2.5" Storage Installation


Space is provided on the bottom of the case for additional installation of 2.5" HDD/SSD.






# Easy Cooler Installation

Separate aperture for CPU cooler is provided for convenient CPU cooler installation without having to remove motherboard from case.






# Specifications


**Z5 Plus**

Model Name		Z5 Plus
Case Type		ATX Mid Tower CASE
Dimensions (W x H x D)		205 x 460 x 490mm
Motherboards		Standard ATX / Micro ATX
Power Supply Unit		Standard ATX / ATX 12V
PCI/AGP Card Compatibility		Full Size (up to 330mm)
Expansion Slots		7 Slots
Drive Bays	External 5.25"	3
	Internal 3.5"	3
	External 3.5	1 (Convertible 1 x Internal 3.5" or 1 x 2.5"SSD)
	Internal 2.5"	2
Cooling Components (2 Fans standard)	Front	1 x 120mm Blue LED Fan
	Rear	1 x 120mm Fan
	Top	1 x 120mm Blue LED Fan
	Bottom	no
Fan Controller		yes (2 channel)
Side Acrylic Tuning		yes
I/O Ports		1 x Microphone
		1 x Headphones
		2 x USB 2.0, 1 x USB3.0


**Z5**

Model Name		Z5
Case Type		ATX Mid Tower CASE
Dimensions (W x H x D)		205 x 460 x 490mm
Motherboards		Standard ATX / Micro ATX
Power Supply Unit		Standard ATX / ATX 12V
PCI/AGP Card Compatibility		Full Size (up to 330mm)
Expansion Slots		7 Slots
Drive Bays	External 5.25"	3
	Internal 3.5"	3
	External 3.5	1 (Convertible 1 x Internal 3.5" or 1 x 2.5"SSD)
	Internal 2.5"	2
Cooling Components (2 Fans standard)	Front	1 x 120mm Blue LED Fan
	Rear	1 x 120mm Fan
	Top	no
	Bottom	no
Fan Controller		no
Side Acrylic Tuning		no
I/O Ports		1 x Microphone
		1 x Headphones
		2 x USB 2.0