

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [50394-8051](#)  
**Status:** **Active**  
**Overview:** [Milli-Grid™ Connector System](#)  
**Description:** [Milli-Grid™ Crimp Terminal, Reel, 0.38µm Select Gold, Lead free](#)

**Documents:**

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)  
[Product Specification PS-51110-001 \(PDF\)](#)

**General**

Product Family	Crimp Terminals
Series	50394
Application	Signal
Crimp Quality Equipment	Yes
Overview	<a href="#">Milli-Grid™ Connector System</a>
Packaging Alternative	<a href="#">50394-8100 (Loose)</a>
Product Literature Order No	987650-1991
Product Name	Milli-Grid™
UPC	800753576193

**Physical**

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Nickel
Net Weight	24.300/mg
Packaging Type	Reel
Plating min - Mating	0.381µm
Plating min - Termination	2.032µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.40mm max.
Wire Size AWG	24, 26, 28, 30
Wire Size mm²	N/A

**Electrical**

Current - Maximum per Contact	0.5A, 1.5A, 1A, 2A
Voltage - Maximum	125V

**Material Info**

**Reference - Drawing Numbers**

Product Specification	PS-51110-001
Sales Drawing	SD-50394-8***, SD-50394-8XXX




image - Reference only

**EU RoHS**

**ELV and RoHS  
Compliant**

**REACH SVHC**

**Contains SVHC: No  
Low-Halogen Status  
Low-Halogen**

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of  
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any  
 non-product compliance questions.

**Search Parts in this Series**

[50394Series](#)

**Use With**

[51110 Crimp Housing](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are  
 found by selecting the products below.  
 Crimp Height Specifications are then  
 contained in the Application Tooling  
 Specification document.*

**Global**

Description	Product #
Hand Crimp Tool for Crimp Terminals	<a href="#">0638190100</a>
FineAdjust™ Applicator for 2.00mm Pitch Wire-to-Board Crimp Terminals 24-30 AWG	<a href="#">0639005200</a>
T2 Terminator Die	<a href="#">0639105200</a>

**Japan**

Description	Product #
-------------	-----------

Applicator for M21 1A 0573153000  
Bench Press, 24-30  
AWG Wire  
Hand Extraction Tool 0011267074

This document was generated on 05/21/2014

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**