


PRODUCT SPECIFICATION

Brand	C.K
Product Range	Tape measures
Catalogue number	3561, 3563 & 3565
Date	19/02/2008

Range Description Long tape measures for construction and surveying
Features 3561; <ul style="list-style-type: none">• Glass fibre reinforced tape – strong and stretch resistant• Tough ABS case• Fold out winding handle for rapid tape rewind• Fold out anchor hook• Hand strap for convenience• 73/362/EEC Class III accuracy. 3563 Tape: <ul style="list-style-type: none">• Steel tape, nylon coated – for superior abrasion resistance and longer life• Tough ABS case• Fold out winding handle for rapid tape rewind• Fold out anchor hook• Hand strap for convenience• 73/362/EEC Class II accuracy - for confident results. 3565 Tape: <ul style="list-style-type: none">• Strong, comfortable and accurate• Glass fibre reinforced tape – strong and stretch resistant• Tough ABS case• Fold out winding handle for rapid tape rewind and convenient storage• Fold out anchor hook• Integral ground spike• 73/362/EEC Class III accuracy.



3561





3563



3565

Item Number	Item Description	EAN No	Commodity code	Carton Qty
T3561 100	Measuring tape 30m/100ft. Fibre tape	5013969964707	90178010	3
T3563 100	Measuring tape 30m/100ft. Steel tape	5013969965100	90178010	3
T3565 100	Surveyors measuring tape 30m/100ft	5013969965209	90178010	3
T3565 165	Surveyors measuring tape 50m/165ft	5013969143904	90178010	3
T3565 330	Surveyors measuring tape 100m/300ft	5013969066838	90178010	3

Technical product information	
Standards compliance	<p>The graduations printed on the tape blade of the 3563 conform to the accuracy requirements of 73/362/EEC Class II</p>  <p>The graduations printed on the tape blade of the 3561 and 3565 range conform to the accuracy requirements of 73/362/EEC Class III</p> 
User health and safety information	None applicable
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	<p>C.K products are guaranteed for life against imperfect materials or workmanship</p> <p>Tape measures contain moving parts that may wear over time, these are not covered under the terms of the warranty</p>
Country of origin	Taiwan

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T3561 100	160	35	160	490	200	40	275	550
T3563 100	160	35	160	790	200	40	275	850

T3565 100	205	45	340	710	205	45	340	730
T3565 165	270	45	410	970	270	45	410	990
T3565 330	310	45	450	1505	310	45	450	1525

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T3561 100	215	385	83	1790		
T3563 100	215	385	83	2690		
T3565 100	225	365	145	2366		
T3565 165	280	425	145	3222		
T3565 330	320	470	145	4867		

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T3561 100	56	Blister	2	Insert			Box	140
T3563 100	56	Blister	2	Insert			Box	140
T3565 100			20	Card			Box	176
T3565 165			20	Card			Box	252
T3565 330			20	Card			Box	292