

## General Information

Extended Product Type:	332RPR6
Product ID:	2CMA168291R1000
EAN:	7392696682916
Catalog Description:	Socket-outlet with RCD, 6h, 30mA, 32A, IP44, 3P+E
Long Description:	Socket-outlet with RCD, earthing sleeve position 6h, 30mA, rated current 32A, IP44 splashproof, 3-poles+earth, frequency 50-60 Hz, color code Red

## Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Socket Outlets with RCD

## Ordering

EAN:	7392696682916
Minimum Order Quantity:	1 piece
Country of Origin:	Czech Republic (CZ)

## Dimensions

Product Net Width:	120 mm
Product Net Height:	243 mm
Product Net Length:	149 mm
Product Net Depth:	243 mm
Product Net Weight:	1.20 kg

## Container Information

Package Level 1 Width:	124 mm
Package Level 1 Length:	337 mm
Package Level 1 Height:	153 mm
Package Level 1 Gross Weight:	1.3 kg
Package Level 1 EAN:	7392696682916
Package Level 1 Units:	1 piece

## Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2007 Q1
--------------	---

## Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	<a href="#">2CMC700005D0001;</a>
Environmental Information:	<a href="#">2CMC700001D0002;</a>
RoHS Information:	<a href="#">2CMC700032;</a>

## Additional Information

Additional Information:	Cable entry, knock-outs 2xØ25mm
Cable Cross-Section:	2.5 ... 10 mm <sup>2</sup>
Cable Entry Position:	Top
Cable Outlets Per Side:	2xØ25
Color:	Red
Degree of Protection:	IP44
Enclosure Material:	Thermoplastic
Frequency (f):	50 Hz 60 Hz
Function:	Surface socket outlet with RCD, 30 mA
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#332RPR6
Number of Poles:	4
Number of RCD 30mA:	1
Number of RCDs:	1
Object Classification Code:	2CMT005069
Product Main Type:	RPR
Product Name:	Industrial Socket Outlet with Protection
Protection Type:	Splashproof
Rated Current (I <sub>n</sub> ):	32 A
Rated Residual Current:	30mA
Rated Voltage (U <sub>r</sub> ):	380 ... 415 V
RoHS Date:	2009-01

<b>Standards:</b>	IEC 60309-1,-2
<b>Suitable For:</b>	Socket Outlets with RCD
<b>Suitable for Product Class:</b>	Industrial Plugs and Sockets

---

### Classifications

---

<b>E-nummer:</b>	2466305
<b>UNSPSC:</b>	39120000

---

