

## 216RAU6

ABB contact for United Kingdom



### General Information

<b>Extended Product Type:</b>	216RAU6
<b>Product ID:</b>	2CMA193218R1000
<b>EAN:</b>	7392696932189
<b>Catalog Description:</b>	Socket-outlet, panel mounting, 6h, 16A, IP44, unified flange, angled, 2P+E
<b>Long Description:</b>	Socket-outlet, panel mounting, earthing sleeve position 6h, rated current 16A, IP44 splashproof, unified flange, angled, 2-poles+earth, frequency 50-60 Hz, color code Blue

### Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Socket Outlets for Panel Mounting

### Ordering

<b>EAN:</b>	7392696932189
<b>Minimum Order Quantity:</b>	10 piece
<b>Country of Origin:</b>	Czech Republic (CZ)

### Dimensions

<b>Product Net Width:</b>	110 mm
<b>Product Net Height:</b>	96 mm
<b>Product Net Length:</b>	110 mm
<b>Product Net Depth:</b>	96 mm
<b>Product Net Weight:</b>	0.24 kg

### Container Information

<b>Package Level 1 Width:</b>	179 mm
<b>Package Level 1 Length:</b>	370 mm
<b>Package Level 1 Height:</b>	152 mm
<b>Package Level 1 Gross Weight:</b>	0.24 kg
<b>Package Level 1 EAN:</b>	7392696932189
<b>Package Level 1 Units:</b>	10 piece

### Environmental

<b>RoHS Status:</b>	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-03-01
---------------------	--

### Certificates and Declarations (Document Number)

<b>Declaration of Conformity - CE:</b>	2CMC700005D0001
<b>Environmental Information:</b>	2CMC700001D0002
<b>RoHS Information:</b>	2CMC700047D0001

### Additional Information

<b>Cable Cross-Section:</b>	1.5 ... 4 mm <sup>2</sup>
<b>Color:</b>	Blue
<b>Degree of Protection:</b>	acc. to IEC 60529 IP44
<b>Enclosure Material:</b>	Thermoplastic
<b>Frequency (f):</b>	50 Hz 60 Hz
<b>Function:</b>	Socket outlet, panel mounting, unified flange, angled
<b>IIT Publishing Status:</b>	Level 0 - Information enabled
<b>Invoice Description:</b>	Ind. P&S#216RAU6
<b>Mounting Type:</b>	unified flange, angled

ABB's website uses cookies. By staying here you are agreeing to our use of cookies. [Learn more](#)

I agree

<b>Number of Poles:</b>	3
<b>Object Classification Code:</b>	2CMT005069
<b>Product Main Type:</b>	RAU
<b>Product Name:</b>	Industrial Socket Outlet Panel Mounting
<b>Protection Type:</b>	Splashproof
<b>Rated Current (I<sub>n</sub>):</b>	16 A
<b>Rated Voltage (U<sub>r</sub>):</b>	200 ... 250 V
<b>RoHS Date:</b>	2009-01
<b>Standards:</b>	IEC 60309-1,-2
<b>Suitable For:</b>	Socket Outlets for Panel Mounting
<b>Suitable for Product Class:</b>	Industrial Plugs and Sockets

---

### Classifications

---

<b>E-number:</b>	2416637
<b>UNSPSC:</b>	39120000

---

