

232RS6

ABB contact for United
Kingdom

General Information

Extended Product Type:	232RS6
Product ID:	2CMA193122R1000
EAN:	7392696931229
Catalog Description:	Surface socket-outlet, 6h, 32A, IP44, 2P+E
Long Description:	Surface socket-outlet, earthing sleeve position 6h, rated current 32A, IP44 splashproof, 2-poles+earth, frequency 50-60 Hz, color code Blue

Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Surface Socket Outlets

Ordering

EAN:	7392696931229
Minimum Order Quantity:	10 piece
Country of Origin:	Czech Republic (CZ)

Dimensions

Product Net Width:	85 mm
Product Net Height:	163 mm
Product Net Length:	118 mm
Product Net Depth:	163 mm
Product Net Weight:	0.300 kg

Container Information

Package Level 1 Width:	173 mm
Package Level 1 Length:	430 mm
Package Level 1 Height:	199 mm
Package Level 1 Gross Weight:	0.331 kg
Package Level 1 EAN:	7392696931229
Package Level 1 Units:	10 piece

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-03-01
---------------------	--

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	2CMC700005D0001
Environmental Information:	2CMC700001D0002
RoHS Information:	2CMC700022

Additional Information

Additional Information:	Cable entry, flexible membrane and metric threaded M25 insert for top cable entry.Rear knock-out cable entry.
Cable Cross-Section:	2.5 ... 10 mm ²
Color:	Blue
Degree of Protection:	acc. to IEC 60529 IP44
Enclosure Material:	Thermoplastic
Frequency (f):	50 Hz 60 Hz
Function:	Surface socket outlet
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#232RS6

ABB's website uses cookies. By staying here you are agreeing to our use of cookies. [Learn more](#)

 I agree

Number of Poles:	3
Object Classification Code:	2CMT005069
Product Main Type:	RS
Product Name:	Industrial Socket Outlet
Protection Type:	Splashproof
Rated Current (I_n):	32 A
Rated Voltage (U_r):	200 ... 250 V
RoHS Date:	2009-01
Standards:	IEC 60309-1,-2
Suitable For:	Surface Socket Outlets
Suitable for Product Class:	Industrial Plugs and Sockets

Classifications

E-nummer:	2416491
UNSPSC:	39120000

