

Title:
Quickset Adjustable Torque Screwdrivers

Key Benefits:

Quickset screwdrivers achieve accurate torque application by eliminating both under and over tightening using Torqueleader’s proven slipping technology. This enables any user to deliver the correct torque with confidence regardless of task and operator skill level

Fast and accurate to set, using the quick and clear to read micrometer setting scale

A single tool can cover a broad variety of applications due to its wide torque range

Long service life is provided through the durable design utilising hard wearing materials such as stainless steel and aluminum

Optional Lock on T-Bar for larger models of screwdriver provides extra leverage when required (Order Code: P29530).

Note: T-Bar is not included with the Quickset Screwdriver Range

Technical Information:

Accuracy +/- 6% of reading
 ISO 6789:2003 Classification 2D

Order Code	Model	Calibration Range		Drive	Range	
		Range				
016000	Quickset Minor Metric SD	20-120 cN.m	1 cN.m	1/4" Square M	160	158
016040	Quickset Minor Metric FH	20-120 cN.m	1 cN.m	1/4" Hex F	169	165
016020	Quickset Minor Imp SD	20-120 ozf.in	1 ozf.in	1/4" Square M	160	158
016060	Quickset Minor Imp FH	20-120 ozf.in	1 ozf.in	1/4" Hex F	169	165
016080	Quickset Minor lbf.in SD	2-12 lbf.in	0.1 lbf.in	1/4" Square M	160	158
016070	Quickset Minor lbf.in FH	2-12 lbf.in	0.1 lbf.in	1/4" Hex F	169	165
016100	Quickset 6 SD	1-6 N.m	0.1 N.m	1/4"	222	340

Square M

016500	Quickset 6 FH	1-6 N.m	0.1 N.m	1/4" Hex F	184	335
016200	Quickset 50 SD	5-50 lbf.in	1 lbf.in	1/4" Square M	222	340
016600	Quickset 50 FH	5-50 lbf.in	1 lbf.in	1/4" Hex F	184	335
016300	Quickset 9 SD	4-9 N.m	0.1 N.m	1/4" Square M	222	340
016700	Quickset 9 FH	4-9 N.m	0.1 N.m	1/4" Hex F	184	335
016400	Quickset 80 SD	30-80 lbf.in	1 lbf.in	1/4" Square M	222	340
016800	Quickset 80 FH	30-80 lbf.in	1 lbf.in	1/4" Hex F	184	335

Order Code	Model	Calibration Range		Drive	160	158
		Range				
016030	Quickset Minor kgf.cm SD	1-12 kgf.cm	0.1 kgf.cm	1/4" Square M	160	158
016050	Quickset Minor kgf.cm FH	1-12 kgf.cm	0.1 kgf.cm	1/4" Hex F	169	165
016130	Quickset 60 K SD	10-60 kgf.cm	1 kgf.cm	1/4" Square M	222	340
016530	Quickset 60 K FH	10-60 kgf.cm	1 kgf.cm	1/4" Hex F	184	335
016330	Quickset 90 K SD	40-90 kgf.cm	1 kgf.cm	1/4" Square M	222	340
016730	Quickset 90 K FH	40-90 kgf.cm	1 kgf.cm	1/4" Hex F	184	335