


**Datasheet**

Art.No. Z7.268.0327.0

Jumper bar IVB WKF 1,5- 3

Cross connector, insulated for DIN rail terminal blocks type WKF..., 3 -pole



|            |               |
|------------|---------------|
| Art.No.    | Z7.268.0327.0 |
| EAN        | 4015573732018 |
| Order unit | 10 pieces     |

**Approvals**

**Technical data**

**General**

|                          |                 |
|--------------------------|-----------------|
| Colour                   | Yellow          |
| Type                     | Cross connector |
| Modular spacing          | 4.2 mm          |
| Number of bridged clamps | 3               |
| Mounting method          | Pluggable       |
| Insulated                | Yes             |

**Accessories**

|                          |                 |
|--------------------------|-----------------|
| Type                     | Cross connector |
| Mounting method          | Pluggable       |
| Insulated                | Yes             |
| Colour                   | Yellow          |
| Number of bridged clamps | 3               |
| Modular spacing          | 4.2 mm          |

Drawings

A  
1  
2  
3  
4  
5  
6  
7  
8  
9  
10  
11  
12  
13  
14  
15  
16  
17  
18  
19  
20  
M1  
M2  
M3  
L  
G  
i  
11.1  
12.1  
1.1

Insolierung  
gelb/  
insulation  
yellow

**Z7.268.0227.0**  
M 1:1

Weitere Daten siehe Katalog  
further data see catalog

| Teile-Nr.<br>part-number | Typ<br>type    | Polzahl<br>pole | L    |
|--------------------------|----------------|-----------------|------|
| Z7.268.0227.0            | IVB WKF 1,5- 2 | 2               | 7,0  |
| Z7.268.0327.0            | IVB WKF 1,5- 3 | 3               | 11,2 |
| Z7.268.0427.0            | IVB WKF 1,5- 4 | 4               | 15,4 |
| Z7.268.0527.0            | IVB WKF 1,5- 5 | 5               | 19,6 |
| Z7.268.1027.0            | IVB WKF 1,5-10 | 10              | 40,6 |
| Z7.268.2027.0            | IVB WKF 1,5-20 | 20              | 82,6 |

|                         |  |                                             |  |                                                                       |  |                   |  |
|-------------------------|--|---------------------------------------------|--|-----------------------------------------------------------------------|--|-------------------|--|
| Freifertigkeit nach DIN |  | CAD - Zeichnung, keine manuellen Änderungen |  | 1. Verwendung: -                                                      |  | Bl.: 1 von 1      |  |
| Maßstab                 |  | Werkstoff und Oberfläche:                   |  | Zeichnung Nr.                                                         |  | Index             |  |
| 5:1                     |  | 2004 Tag                                    |  | T                                                                     |  | Z7.268.0227.0 01K |  |
| Entworfen               |  | 09.11.                                      |  | Schmitt J.                                                            |  |                   |  |
| Geprüft                 |  | -                                           |  | -                                                                     |  |                   |  |
| Nenngr.                 |  | -                                           |  | -                                                                     |  | Ersatz für: -     |  |
|                         |  | <b>Typ</b><br>IVB<br>WKF 1,5-...            |  | <b>Benennung</b><br><b>VERBINDUNGSSTECKER</b><br>insulated jumper bar |  |                   |  |
| Änderung                |  | Werkstoffliche<br>Veränderungen             |  |                                                                       |  |                   |  |

Z7.268.0227.01K\_4 DWK028 Schmitt 2004-11-09 10:33:52 1:000