

# HL 2010 E

Professional Heat Guns with Electronic Thermocouple Control



 Double Insulated



## HG 2010 E Specifications

Item No.	34850 34851 with case
Temperature	120°F - 1150°F (49°C - 621°C)
Airflow	3.6 / 10.6 / 17.6 cfm
3 Stage Switch	cool air stage 120°F / 3.6 cfm variable temperature 10.6 cfm variable temperature 17.6 cfm
Element	DuraTherm™ ceramic heating element
Output	1500 watts
Voltage	120 VAC / 60 Hz
Amps	12.5
Power Cord	industrial grade rubber, length: 6 ft
Nozzle Diameter	1.3" (33.02 mm)
Net Weight	2.1 lbs (33.3 oz)
Dimensions	10.2" x 3.5" x 8.0" (l x w x d)
Single Sell Pack	dimensions: 11.4" x 9.5" x 3.7" weight: 2.6 lbs (41.0 oz)
Warranty	one year limited
Certifications	C-UL-UL Listed, RoHs Compliant, ISO 9001:2001 Made in E.U.

### HL 2010 E Heat Gun with LCD Temp Display

HL 2010 E Heat Gun is microprocessor controlled and features an LCD display which enables temperature selection in 10°F increments. Exclusive DuraTherm™ heating element ensures even heat and product longevity.

### Applications

The HL 2010 E is suitable for applying shrink tubing/connectors, activating/softening adhesives, working heat sensitive materials and other applications requiring a specific temperature.

### Key Features:

- Microprocessor controlled
- Duratherm™ heating element
- LCD display
- Ergonomically designed
- Double insulated
- Reduction nozzles are approved for use on Professional Heat Guns with electronic thermocouple control



Temperature



3 Stage Switch  
Cool / Low / High



Dual Air Filters



DuraTherm™  
Heating Element



Soft Grip Handle



Rubber Stand



www.steinell.net

# HG 2010 E

Professional Heat Guns with Electronic Thermocouple Control



## Industry Specific Kits Available



### Automotive Kit

- HG 2010 E Heat Gun
  - TS 600
  - Welding Iron
  - 9 mm Reducer
  - 20 mm Reducer
  - 2 pcs Wire Mesh
  - 16 pcs ThermoFlex Rod
  - Temperature Guard
  - Guide Book
  - Heavy Duty Case
- No. 34853



### Plastic Welding Kit

- HG 2010 E Heat Gun
  - 39 mm Reflector
  - 9 mm Reducer
  - Welding Tip
  - 20 mm Lap Welding Tip
  - Welding Rod Assortment:  
ABS, PP, PVC LDPE, HDPE
  - Guide Book
  - Heavy Duty Case
- No. 34854



### Multi-Purpose Kit

- HG 2010 E Heat Gun
  - 9 mm Reflector
  - 14 mm Reflector
  - 39 mm Reflector
  - 9 mm Reducer
  - Overhead Hanger
  - Welding Rod Assortment:  
ABS, PP, PVC, LDPE, HDPE
  - Heavy Duty Case
- No. 34856



### HL 2010 in Case

- HG 2010 E Heat Gun
  - Heavy Duty Case
- No. 34851

## Accessories for a Variety of Applications

Visit [www.steinell.net](http://www.steinell.net) for our full line of accessories



### Pinpoint Reducer

3.3" x 1.5" x 1.5"  
No. 07082



### 9 mm Reducer Nozzle

2.5" x 1.5" x 1.5"  
No. 07062



### 14 mm Reducer Nozzle

2.5" x 1.5" x 1.5"  
No. 07071



### Temperature Guard

3.2" x 3.2" x .01"  
No. 07381



### Wire Mesh

10.0" x 5.0" x 0.2  
No. 07371



### 9 mm Reflector Nozzle

3.4" x 1.5" x 1.5"  
No. 07061



### 14 mm Reflector Nozzle

2.3" x 1.5" x 1.5"  
No. 07461



### Welding Iron

2.5" x 1.5" x 1.0"  
No. 07361



### Plastic Welding Nozzle

2.0" x 1.3" x .4"  
No. 07091



### Welding Nozzle

2.6" x 1.2" x .5"  
No. 07531



### 20 mm Lap Welding Slit Tip

2.0" x 0.8" x 0.4"  
No. 07101



**ThermoFlex™  
Welding Rods**  
12" x 1.1" x 0.6"  
No. 07352



**HDPE Plastic  
Welding Rods**  
9.0" x 1.5" x 0.4"  
No. 07121



**Rigid PVC  
Welding Rods**  
9.0" x 1.5" x 0.4"  
No. 07311



**LDPE Plastic  
Welding Rods**  
9.0" x 1.5" x 0.4"  
No. 07331



**PP Plastic  
Welding Rods**  
9.0" x 1.5" x 0.4"  
No. 07341



**ABS Plastic  
Welding Rods**  
9.0" x 1.5" x 0.4"  
No. 07421