

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [19067-0082](#)
Status: **Active**
Overview: Ring Tongue - Spade Terminals
Description: NylaKrimp™ Funnel Entry Ring Tongue Terminal for 4 AWG Wire, Stud Size 1/4" (M6)

Documents:

3D Model	Product Specification PS-19902-013 (PDF)
Drawing (PDF)	Product Specification PS-19902-016 (PDF)
Product Specification PS-19902-011 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR18689
UL	E32244

General

Product Family	Ring and Spade Terminals
Series	19067
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	Ring Tongue - Spade Terminals
Product Name	NylaKrimp™
Type	Ring
UPC	800753066526

Physical


Barrel Type	Closed - Brazed
Flammability	94V-2
Insulation	Nylon (PA)
Material - Plating Mating	Tin
Net Weight	9.593/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	1/4" (M6)
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	12.95mm max.
Wire Size AWG	4

Material Info

Old Part Number	F-967-14
-----------------	----------

Reference - Drawing Numbers

Product Specification	PS-19902-011, PS-19902-013, PS-19902-016
Sales Drawing	SD-19067-018



EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[19067Series](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool	0640013900
Putt Pump Dieless Head System	0192860065
Manual Putt Pump Hydraulic System, Die set required	0192860117
Hand Crimp Tool for 4 AWG Insulated Ring Terminals	0640017870
Die Set (large) for the HHLS Hydraulic Crimper	0192890007

This document was generated on 06/30/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION