

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [50147-8000](#)
Status: **Active**
Overview: Mizu-P25™ Miniature Waterproof Connectors
Description: 2.50mm Pitch Mizu-P25™ Crimp Terminal, 50147, Reel

Documents:

[3D Model](#) [Application Specification AS-50147-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-52213-003 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	50147
Application	Signal
Crimp Quality Equipment	Yes
Overview	Mizu-P25™ Miniature Waterproof Connectors
Packaging Alternative	50147-8100 (Loose)
Product Name	Mizu-P25™ Waterproof
UPC	800754369374

Physical

Gender	Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	55.800/mg
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.40-1.70mm
Wire Size AWG	20, 22
Wire Size mm²	N/A

Electrical

Voltage - Maximum	125V
-------------------	------

Material Info

Reference - Drawing Numbers

Application Specification	AS-50147-001
Product Specification	PS-52213-003, RPS-501202-001, RPS-52213-002, RPS-52266-001
Sales Drawing	SD-50147-001




image - Reference only

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

**Contains SVHC: No
Low-Halogen Status
Low-Halogen**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[50147Series](#)

Mates With

[Mizu-P25™ Male Housing 50148](#)

Use With

[52266 Mizu-P25™ Crimp Housings](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool	0638118600
FineAdjust™	0639020500
Applicator for 2.5 Mini Splash Proof Crimp Terminal	
T2 Terminator	0639120500
for. Splash Proof	

Wire-to-Wire Crimp Terminal	
Extraction Tool	<u>0638132700</u>
Japan	
Description	Product #
Applicator for M211A	<u>0571443000</u>
Bench Press	

This document was generated on 07/10/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION