

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [19420-0004](#)  
**Status:** **Active**  
**Overview:** [MX150L™ Industrial Sealed Connector System](#)  
**Description:** [MX150L™ Female Terminal for 18-22 AWG Wire, Gold Plated, Metal Strip Carrier](#)

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-19417-001 \(PDF\)](#) [Product Literature \(PDF\)](#)

**Agency Certification**

CSA LR18689  
 UL E152602

**General**

Product Family Crimp Terminals  
 Series [19420](#)  
 Application Power  
 Comments UL E152602  
 Crimp Quality Equipment Yes  
 Overview [MX150L™ Industrial Sealed Connector System](#)  
 Product Literature Order No 987650-2181  
 Product Name MX150L™  
 UPC 822348371884

**Physical**

Flammability 94V-0  
 Gender Female  
 Material - Metal High Performance Alloy (HPA)  
 Material - Plating Mating Gold  
 Material - Plating Termination Tin  
 Net Weight 0.184/g  
 Packaging Type Reel  
 Plating min - Mating 0.762µm  
 Plating min - Termination 2.540µm  
 Termination Interface: Style Crimp or Compression  
 Wire Insulation Diameter 2.36-2.74mm  
 Wire Size AWG 18, 19, 20, 22  
 Wire Size mm² N/A

**Material Info**

**Reference - Drawing Numbers**

Product Specification PS-19417-001  
 Sales Drawing SD-19420-001




image - Reference only

**EU RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC Contains SVHC: No**  
**Low-Halogen Status Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[19420Series](#)

**Mates With**

[19417](#)

**Use With**

[19418](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Hand Crimp Tool	<a href="#">0638117600</a>
Hand Crimp Tool	<a href="#">0638114400</a>
FineAdjust™ for	<a href="#">0639008400</a>
Female Terminal 18-24 AWG Wire	
T2 Terminator for Crimp Terminal,	<a href="#">0639108400</a>

Female 18-24 AWG  
Wire  
Manual Extraction [0638131500](#)  
Tool

This document was generated on 06/30/2014

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**