

Fusedrawer for Fuse Links 5x20 mm resp. 6.3x32 mm

Standard or Medical Fuse drawer



Fuse drawer "Fingergrip" with voltage selector
(Fuse links not enclosed)

Fuse drawer "Extrasafe" without voltage selector
(Fuse links not enclosed)



Description

- Component:
Snap-in, Rear Mounting
- 2 Functions:
Fuseholder for Fuse-links 5x20 mm or 6.3x32 mm, Voltage selector insert
- Approved together with power entry module

Characteristics

- Fuse drawer meets requirements of medical standard IEC/EN 60601-1
The fuse drawer "Fingergrip" can be removed by hand
For added safety "Extra-Safe" fuse drawers are available
With spare fuse compartment
- Suitable for use in equipment according to IEC/UL 60950

Other versions on request

- Fuse drawer with other voltage values

References

Fits to type: [CD](#); [CD-Bowdencable](#); [KD](#); [KD-Bowdencable](#); [KEC](#); [KFC](#)

Weblinks

[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [Approvals](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [Mating Connectors](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [CAD-Drawings](#), [Accessories](#), [Detailed request for product](#)

Voltage Selector Inserts

Index	Marking on Voltage Selector Insert / Terminal No.					
	KEC	1	2	3	4	
yy	KD	3	4	5	6	
00		-	-	-	-	
01		100	120	220	240	
02		110	150	220	-	
03		110	-	220	-	
04		110	220	240	-	
05		115	-	230	-	
06		117	220	240	-	
08		110 V	-	220 V	-	
09		220	-	240	-	
10		115	220	240	-	
11		110	120	220	240	
12		115	230	240	-	
13		100	110	220	240	
14		100	117	220	240	
15		100	115	230	-	
16		100	120	230	240	
17		115	120	230	240	
18		115	-	240	-	
19		220	120	240	230	
20		100	120	230	-	
21		100	-	220	-	
22		100	120	220	230	
23		100	110	120	-	
24		200	220	240	-	

Index yy	KEC KD	Marking on Voltage Selector Insert / Terminal No.			
		1	2	3	4
		3	4	5	6
25		120	-	230	-
27		115	200	230	-
28		-	230	240	-
29		100	117	125	-
30		117	220	240	100
31		117	220	240	100
32		100	110	230	240
34		110	115	230	240
35		100	115	230	240
36		100	110	200	230
37		115	230	240	100
38		110	230	220	240
39		220	230	240	-
40		100	110	127	230
42		100	115	120	230
43		911	-	08Z	-
44		100	115	127	230
45		100	115	230	127
46		100	120	200	230
48		100	120	208	230

Index "yy" matches the last two characters of the Order Number within the Variants

All Variants

Mounting	Fuse-Link	Fuseholder	Comment	Order Number
Fingergrip	5 x 20	1-pole	-	4303.2114.yy
Extra-Safe	5 x 20	1-pole	-	4303.2124.yy
Fingergrip	5 x 20	1-pole	-	4303.2406
Extra-Safe	5 x 20	1-pole	-	4303.2408
Fingergrip	5 x 20	1-pole	spare fuse case	4303.2416
Fingergrip	5 x 20	2-pole	-	4303.2014.yy
Extra-Safe	5 x 20	2-pole	-	4303.2024.yy
Fingergrip	5 x 20	2-pole	-	4303.2401
Extra-Safe	5 x 20	2-pole	-	4303.2403
Fingergrip	5 x 20	2-pole	shorting bar on the neutral side	4303.2036.yy
Extra-Safe	5 x 20	2-pole	shorting bar on the neutral side	4303.2037.yy
Fingergrip	5 x 20	2-pole	shorting bar on the neutral side	4303.2411
Extra-Safe	5 x 20	2-pole	shorting bar on the neutral side	4303.2413
Fingergrip	6.3 x 32	1-pole	-	4303.2614.yy
Extra-Safe	6.3 x 32	1-pole	-	4303.2624.yy
Fingergrip	6.3 x 32	1-pole	-	4303.2906
Extra-Safe	6.3 x 32	1-pole	-	4303.2908
Fingergrip	6.3 x 32	2-pole	-	4303.2514.yy
Extra-Safe	6.3 x 32	2-pole	-	4303.2524.yy
Fingergrip	6.3 x 32	2-pole	-	4303.2901
Extra-Safe	6.3 x 32	2-pole	-	4303.2903
Fingergrip	6.3 x 32	2-pole	shorting bar on the neutral side	4303.2536.yy
Extra-Safe	6.3 x 32	2-pole	shorting bar on the neutral side	4303.2537.yy
Fingergrip	6.3 x 32	2-pole	shorting bar on the neutral side	4303.2911
Extra-Safe	6.3 x 32	2-pole	shorting bar on the neutral side	4303.2913

"yy" see Voltage Selector Inserts Table

Packaging unit 50 Pcs

22.07.2014