

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [19199-0008](#)  
**Status:** **Active**  
**Description:** Avikrimp™ Window Butt Connector for 18-22 AWG Wire, Mylar Tape Carrier

**Documents:**

[Drawing \(PDF\)](#) [Product Specification PS-19902-015 \(PDF\)](#)  
[Product Specification PS-19902-011 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Splices
Series	19199
Comments	Mil Spec M7928/5-3
Crimp Quality Equipment	Yes
Mil-Spec	M7928/5-3
Product Name	Avikrimp™, Butt - Window
UPC	800753046818

**Physical**

Barrel Type	Closed
Color - Resin	Red
Insulation	Nylon (PA)
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.194/g
Packaging Type	Adhesive Tape on Reel
Temperature Range - Operating	-55°C to +105°C
Wire Insulation Diameter	3.56mm max.
Wire Size AWG	18, 20, 22
Wire Size mm²	0.25 - 1.50

**Electrical**


Voltage - Maximum	300V
-------------------	------

**Material Info**

Old Part Number	WA-840T
-----------------	---------

**Reference - Drawing Numbers**

Product Specification	PS-19902-011, PS-19902-015
Sales Drawing	SD-19199-003



**EU RoHS**

**ELV and RoHS  
Compliant**

**REACH SVHC**

**Contains SVHC: No**

**Low-Halogen Status**

**Low-Halogen**

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of  
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any  
 non-product compliance questions.

**Search Parts in this Series**

19199Series

**Application Tooling | FAQ**

*Tooling specifications and manuals are  
 found by selecting the products below.  
 Crimp Height Specifications are then  
 contained in the Application Tooling  
 Specification document.*

**Global**

<b>Description</b>	<b>Product #</b>
Mini-Mac Applicator	<a href="#">0638859100</a>
Air Feed-Mylar Tape Crimp Dies for MTA-100 Tape Applicator used in 3BF Press, MTA-105 Tape Applicator used in TM-2000™ Press, and ATP-301 Air Crimping Press for Mylar Tape Mounted Terminals	<a href="#">0192880043</a>

This document was generated on 06/30/2014

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**