

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [19121-0027](#)
Status: **Active**
Overview: Ring Tongue - Spade Terminals
Description: InsulKrimp™ Flanged Spade Tongue Terminal for 14-16 AWG Wire, Stud Size 6 (M3.5), Mylar Tape Carrier

Documents:

[Drawing \(PDF\)](#)
[Product Specification PS-19902-009 \(PDF\)](#)
[Product Specification PS-19902-011 \(PDF\)](#)
[Product Specification PS-19902-015 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
UL E32244

General

Product Family Ring and Spade Terminals
Series [19121](#)
Crimp Quality Equipment Yes
Mil-Spec N/A
Overview [Ring Tongue - Spade Terminals](#)
Product Name InsulKrimp™
Type Spade
UPC 800753095595

Physical

Barrel Type Closed
Color - Resin Natural
Flammability 94V-0
Insulation PVC
Material - Plating Mating Tin
Net Weight 0.766/g
Packaging Type Adhesive Tape on Reel
Plating min - Mating 4.064μm
Plating min - Termination 4.064μm
Stud Size 6 (M3.5)
Wire Insulation Diameter 4.45mm
Wire Size AWG 14, 16
Wire Size mm² 1.00 - 2.50

Material Info

Old Part Number BB-216-06XT

Reference - Drawing Numbers

Product Specification PS-19902-009, PS-19902-011, PS-19902-015
Sales Drawing SD-19121-001




image - Reference only

Series

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[19121Series](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Crimp Dies for MTA-100 Tape Applicator used in 3BF Press, MTA-105 Tape Applicator used in TM-2000™ Press, and ATP-301 Air Crimping Press for Mylar Tape Mounted Terminals Mini-Mac™ Applicator [0192880123](#) [0638850400](#)

This document was generated on 07/10/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION