












Mobile Air Conditioners Systems

Our high performance portable air conditioner features the latest energy saving technology. Fitted with easy-roll castors it can be conveniently moved from room to room as required. A ducted exhaust hose is included with the system to vent the hot air to the outside of the building. An adjustable window mounting panel is also supplied to attach the exhaust hose for ease of use. This unit benefits from an automatic inbuilt condensate pump, which pumps the water out with the exhaust air, so there is no water tank to empty.

FEATURES

-  Remote control with luminous nightLight
-  High efficiency performance
-  Adjustable fan speeds for rapid cooling or minimum noise
-  Heat-pump model provides heating as well as cooling
-  Plug & Play anywhere operation
-  Oscillating air vanes for dissipation of cold air
-  A timer feature that will turn the unit on and off automatically
-  High efficiency air filters to remove odours and particles
-  Anti-mould coating for hygienic operation
-  Digital display to show operational settings and temperature
-  A "Smart Air" feature that will recall previous settings at the push of a button


SPECIFICATIONS

Model	KYR35/X1C
Power Rating (Ph-V-Hz)	220-240V / 50Hz
Capacity BTU/H (cooling) kW	12500 (3.5kW)
Capacity BTU/H (heating) kW	12700 (3.7kW)
Power Input (W) Cooling/Heating	1250/1345
Current Input (A) Cooling/Heating	5.5/6.0
EER (BTU/hr.w)	2.8
COP (W/W)	3.04
Noise Level dB(A)	56
Dehumidification (L/h)	1.2
Airflow (m3/h)	480
Net Dimension (mm) W/D/H	600x480x830
Net Weight (kg)	42
Max Room Size (m ²)	25m sq
Max Conservatory Size (m ²)	12m sq
Exhaust Hose Length (m)	2m
Exhaust Hose Diameter (mm)	150mm
Window Extraction Kit	Yes



TOSHIBA
COMPRESSOR

All ACC product's are guaranteed for 12 months (unless otherwise stated) from the date of original purchase.



airconditioningcentre®

Copyright © 2002 – 2011 Air Conditioning Centre / Martin Industries
Air Conditioning Centre is a registered trademark of Martin Industries Ltd. E&OE. Registered in England & Wales Co. No. 05436428

Martin Industries Ltd
Unit 10
Milton Business Centre
Wick Drive
New Milton
Hampshire
BH25 6RH
United Kingdom

Telephone: 0370 33 44 55 6
Fax: 0870 33 44 55 9

Email: info@airconditioningcentre.com
Website: www.airconditioningcentre.com