
Vinyl-Insulated (Easy Entry) Spade Terminals

multicomp






Specifications:

Max. Electric Current

Type Termination Method Contact Plating Insulator Material Max. Electrical Rating Terminal Material



: Tin

Tin

: Nylon

- : 105°C 600V
- : Copper

Dimensions								Part
d2	w	F	L	E	D	d1	Т	Number
0.126 (3.2)	0.224 (5.7)						0.03 (0.75)	MC29608
0.146 (3.7)	0.252 (6.4)					0.067 (1.7)		MC29610
								MC29616
								MC29623
	0.283 (7.2)		0.874 (22.2)	0.441 (11.2)	0.157 (4)			MC29612
0.169 (4.3)								MC29625
	0.319 (8.1)							MC29617
		.1)						MC29614
0.209 (5.3)								MC29627
	0.374 (9.5)							MC29618
0.146 (3.7)	0.236 (6)	0.256 (6.5)	0.886 (22.5)	0.453 (11.5)	0.177 (4.5)	0.091 (2.3)	0.031 (0.8)	MC29611
0 146 (2 7)	0.236 (6)							MC29619
0.146 (3.7)	0.283 (7.2)							MC29624
0.169 (4.3)		0.283 (7.2)						

Dimensions : Inches (Millimetres)



www.element14.com www.farnell.com www.newark.com

Vinyl-Insulated (Easy Entry) Spade Terminals



Dimensions								Part
d2	W	F	L	E	D	d1	Т	Number
0 160 (4 3)	0.283 (7.2)							MC29626
0.169 (4.3)								MC29620
	0.311 (7.9)	0.256 (6.5)	0.886 (22.5)	0.453 (11.5)	0.177 (4.5)	0.091 (2.3) 0	0.031 (0.8)	MC29615
0.209 (5.3)								MC29628
	0.366 (9.3)							MC29621
0.169 (4.3)	0.254 (0)	0.276 (7)	1.047 (26.6)	0.555 (14.1)	0.248 (6.3)	0.134 (3.4)	0.039 (1)	MC29622
0.209 (5.3)	0.354 (9)	0.276 (7)						MC29609

Part Number Table

Description	Wire Range AWG mm ²	Stud Size	Colour	Part Number
		#4		MC29608
	22-16 AWG 0.5-1.5 mm ²	#6	Red	MC29610
				MC29616
				MC29623
		#8		MC29612
				MC29625
				MC29617
		#10		MC29614
				MC29627
				MC29618
Terminal, Spade / Fork, Crimp	16-14 AWG 1.5-2.5 mm²	#6	Blue	MC29611
				MC29619
				MC29624
		#8		MC29613
				MC29626
				MC29620
		#10		MC29615
				MC29628
				MC29621
	12-10 AWG	#6	Yellow	MC29622
	4-6 mm ²	#10		MC29609

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage resulting from any reliance on the Information or use of it (including liability resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

www.element14.com www.farnell.com www.newark.com

