

3M™ ESD Warning Labels and 3M™ Signs

Product Selection Guide

Labels alert personnel handling bags, boxes or other carriers that the contents are static-sensitive. 3M ESD Warning Labels provide the ESD symbol and warning message. Destructible-type labels are “tamper evident,” allowing personnel to monitor if a bag has been opened. Reusable type labels allow personnel to reopen the bag without tearing the label.

3M Signs and 3M™ Aisle Marking Tape may be used to clearly identify the areas requiring static protective measures. Apply them to doors, floors, walls, tote boxes, or to any area to indicate static sensitive parts.



See product photos on the next page.

Product Type	Part Number	Description	Photo Number
Attention Label - Destructible	7102	Yellow w/ Black Type. Room to write. Static Warning Symbol. Size: 1.875 in. x 2.5 in. (4.8 cm x 6.4 cm) 500 per roll	1
Attention Label - Destructible	ALABEL	Yellow w/ Black Type. Room to write. Static Warning Symbol. Size: 1.875 in. x 2.5 in. (4.8 cm x 6.4 cm) 500 per roll	2
Attention Label - Destructible	ALABEL5/8x2	Yellow w/ Black Type. Static Warning Symbol. Size: 0.625 in. x 2.0 in (1.6 cm x 5.1 cm) 1000 per roll	3
Caution Label - Destructible	CLABEL2X2	Yellow w/ Black Type. Displays force-arrows and warning. Size: 2 in. x 2 in. (5.1 cm x 5.1 cm) 500 per roll.	4
Caution Label - Destructible	CLABEL4X4	Yellow w/ Black Type. Displays force-arrows and warning. Size: 4 in. x 4 in. (10.2 cm x 10.2 cm) 100 per roll.	5
Military Label - Destructible	7202	Yellow w/ Black Type. MIL-STD-129N Symbol Size: 2 in. x 2 in. (5.1 cm x 5.1 cm) 500 per roll	6
Military Label - Destructible	129LABEL	Yellow w/ Black Type. MIL-STD-129N Symbol Size: 2 in. x 2 in. (5.1 cm x 5.1 cm) 500 per roll	7
RoHS Label - Destructible	ROHSLABEL	Green/White Type. Size: 1.75 in. x 1.75 in. (4.5 cm x 4.5 cm) 500 per roll	8
Attention Label -Reusable	7101	Orange w/ Black Type. Static Warning Symbol. Size: 1.875 in. x 2.5 in. (4.8 cm x 6.4 cm) 500 per roll	9
Military Label -Reusable	7201	Yellow w/ Black Type. MIL-STD-129N Symbol Size: 4 in. x 4 in (10.2 cm x 10.2 cm)	10
Barrier Bag Label 113 - Destructible	113LABEL	White w/ Blue Type. for use with IPC/JEDEC J-STD-033 and JEDEC113. 4 in. x 4 in. (10.2 cm x 10.2 cm) 100 per roll	11
Barrier Bag Label -Destructible	DRILABEL	Yellow w/ Black Type. Displays static and moisture warning symbols. Provides writing space. 4 in. x 5 in. (10.2 cm x 12.7 cm) 100 per roll	12
ESD Warning Sign	ESDSIGN4X10	Yellow w/ Black Type. Displays static warning symbol. 4 in. x 10 in. (10.2 cm x 25.4 cm)	13
ESD Warning Sign	ESDSIGN8.5X11	Yellow w/ Black Type. Displays static warning symbol. 8.5 in. x 11 in. (21.6 cm x 27.9 cm)	14
ESD Warning Poster	SIGN17X22E	Yellow w/ Black Type. Displays static warning symbol. 17 in. x 22 in. (43.2 cm x 55.9 cm) 5 per box	15
Aisle Marking Tape	AISLETAPE54	Yellow w/ Black Type. Self stick plastic tape. Rolls are 3 in. (7.6 cm) wide and 54 ft. (16.5 m) long	16

3M™ ESD Warning Labels and 3M™ Signs

Product Selection Guide

See product descriptions on the first page.

1. 7102



2. ALABEL



3. ALABEL5/8X2



4. CLABEL2X2



5. CLABEL4X4



6. 7202



7. 129LABEL



8. ROHSLABEL




9. 7101




10. 7201



11. 113LABEL



12. DRILABEL



13. ESDSIGN4X10



14. ESDSIGN8.5X11



15. SIGN17X22E



16. AISLETAPE54



See 3M static control products, data sheets, and more at 3Mstatic.com

3M is a trademark of 3M Company.

In the event any product is proven not to conform with 3M's Regulatory Information, then 3M's entire liability and Buyer's exclusive remedy will be in accordance with the Warranty stated below.

Important Notice

Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use.

Warranty; Limited Remedy; Limited Liability.

3M's product warranty is stated in its Product Literature available upon request. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.



Electronic Solutions Division Static Control Products

926 JR Industrial Drive
Sanford, NC 27332-9733
Toll-Free: 866-722-3736
International: 919-718-0000
Email: 3mstaticinfo@mmm.com
www.3Mstatic.com

Please recycle. Printed in USA.
© 3M 2013. All rights reserved.
98-0799-1105-7 JHA