

Micro SD to Micro USB / USB OTG Adapter Card Reader For Android Devices

StarTech ID: MSDREADU2OTG



The MSDREADU2OTG Micro SD to USB/Micro USB Adapter lets you turn a Micro SD card into an external USB storage solution that can interface with any USB-enabled computer or OTG-enabled device, such as Samsung Galaxy smartphones and tablets.

Expand the storage capabilities of your OTG-enabled smartphone or tablet, by creating an external storage device that you can also connect to your USB-enabled computer, and transfer files from one device to another with standard USB and Micro USB interface options.

Maximize portability by creating a compact, external storage solution that you can connect to your smartphone, tablet or laptop computer. For a hassle-free setup, the OTG adapter supports plug-and-play installation and is natively supported by any USB-enabled computer or any OTG-enabled mobile device.

The MSDREADU2OTG is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Expand the Storage Capability
of your OTG-enabled Smartphone or Tablet



Connect
to your Computer or Mobile Device



Converts Micro SD to standard USB
or Micro USB (OTG) devices.

Applications

- Expand available storage on your smartphone by adding an OTG storage drive
- Quickly transfer files to your smartphone or tablet without connecting to a computer or network
- Turn an unused Micro SD card into a ultra-portable USB storage solution
- Take your important data with you on an SD card and access it from your computer or smartphone when you need it

Features

- Converts Micro SD to standard USB or Micro USB
- Compatible with OTG-enabled Smartphones and USB-enabled computers
- Small, lightweight design
- Plug-and-play installation
- Universal power adapter included

Technical Specifications

Warranty	2 Years
Bus Type	USB 2.0
Number of Drives	1
Drive Installation	Fixed
Chipset ID	Genesys - GL823
Drive Connectors	1 - MicroSD Receptacle
Host Connectors	1 - USB A (4 pin) Male
Host Connectors	1 - USB Micro-B (5 pin) Male
Maximum Data Transfer Rate	480 Mbps
Type and Rate	USB 2.0 - 480 Mbit/s
UASP Support	No
Max Drive Capacity	Tested with MSD cards up to 64GB
Memory Media Type	Mini-SD, Micro-SD (Mini/Micro Secure Digital)
OS Compatibility	Windows® 8/8.1 (32/64bit), 7 (32/64bit), Server 2008 (32/64), Vista(32/64), Server 2003 (32/64) XP(32/64), 2000 Apple® Mavericks (10.9) OSX Mountain Lion (10.8), Lion (10.7), Snow Leopard (10.6) Linux Google Chrome™ OS Android
Product Length	40 mm [1.6 in]
Product Width	12 mm [0.5 in]
Product Height	5 mm [0.2 in]
Product Weight	4 g [0.1 oz]
Operating Temperature	0°C to 50°C (32°F to 122°F)
Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Humidity	5% ~ 80% RH
Shipping (Package) Weight	24 g [0.8 oz]
Included in Package	1 - Micro SD to USB / Micro USB OTG Adapter

Certifications, Reports and Compatibility

