

Count Down Timers

Save Energy with Timer Controls

- Digital accuracy
- Simple “one button” selection
- Matches Hubbell Energy Control sensors



FEATURES

- Pre-set 5 button selection
- Manual override to off
- LEDs count down as time intervals reduce
- “Alert to off” function - Red LED will flash during the final 30 seconds and emit audible warning
- Permanent time markings

SPECIFICATIONS

- Rating:
 - 120V AC - 8.3A, Resistive or Inductive (1000W Incandescent), 1/6 hp
 - 277V AC - 5.1A, Inductive (1400W Fluorescent)
- 3 Timer increments: 30 minute, 60 minute, 12 hour
- Operating temperature, 32° F to 122° F (0° C to 50° C)
- Terminates with 6 inch wire leads
- Ashrae, LEED and Cal Tittle 24 eligible
- cULus listed to UL60730-1 and UL60730-2

Timers are used in many commercial, industrial and residential designs as a method to control energy. As an alternative to sensors or building controls, individual switch timers target point-of-use to enable the user to take control of the space and load, within limits. Preset timers are a simple on/off option to consider. By selecting a timer, the maximum on-time is established and control is maintained based on a pre-established regimen, adding to the building's efficiency and energy savings. Timers in increments up to 30 and 60 minutes are excellent for use in indoor spaces. The 12 hour version is popular with outdoor lighting control and HVAC where more on-time is required.



ORDERING INFORMATION

30 Minute Timer

Description	Rating	Color	Catalog Number
Count Down Timer Wall Switch Buttons: Off, 5, 10, 20, 30	120V AC - 8.3A, Resistive or Inductive (1000W Incandescent), 1/6 hp 277V AC - 5.1A, Inductive (1400W Fluorescent)	Ivory Light Almond White	DT5030I DT5030LA DT5030W

60 Minute Timer

Description	Rating	Color	Catalog Number
Count Down Timer Wall Switch Buttons: Off, 15, 30, 45, 60	120V AC - 8.3A, Resistive or Inductive (1000W Incandescent), 1/6 hp 277V AC - 5.1A, Inductive (1400W Fluorescent)	Ivory Light Almond White	DT5060I DT5060LA DT5060W

12 Hour Timer

Description	Rating	Color	Catalog Number
Count Down Timer Wall Switch Buttons: Off, 2, 4, 8, 12	120V AC - 8.3A, Resistive or Inductive (1000W Incandescent), 1/6 hp 277V AC - 5.1A, Inductive (1400W Fluorescent)	Ivory Light Almond White	DT5012I DT5012LA DT5012W



DIMENSIONS Inches (mm)

