

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

53047-1110

Status:

Active

Overview:

PicoBlade™ Connector System

Description:

1.25mm Pitch PicoBlade™ Wire-to-Board Header, Vertical, with Friction Lock, 11 Circuits

Documents:

3D Model

Drawing (PDF)

Product Specification PS-51021-010 (PDF)

Packaging Specification SPK-53047-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Application

Overview

Product Name

UPC

PCB Headers

53047

Signal, Wire-to-Board

PicoBlade™ Connector System

PicoBlade™

800753565869

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Durability (mating cycles max)

First Mate / Last Break

Flammability

Glow-Wire Compliant

Guide to Mating Part

Keying to Mating Part

Lock to Mating Part

Mated Height

Material - Plating Mating

Material - Plating Termination

Net Weight

Number of Rows

Orientation

PC Tail Length

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Polarized to PCB

Shrouded

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

No

11

11

30

No

94V-0

No

No

None

Yes

5.20mm

Tin

Tin

218.000/mg

1

Vertical

2.30mm

No

None

0.80mm

Tray

1.25mm

No

Fully

No

No

-40°C to +85°C

Through Hole

Electrical

Current - Maximum per Contact

Voltage - Maximum

1A

125V

Material Info




image - Reference only

Series

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

53047Series

Mates With

51021 PicoBlade™ Wire-to-Wire

Reference - Drawing Numbers

Packaging Specification
Product Specification

SPK-53047-001
PS-51021-010, RPS-51021-007, RPS-51021-011,
RPS-51021-041, RPS-51021-059, RPS-51021-060,
RPS-51021-071, RPS-51021-089, RPS-51021-104
SD-53047-**10

Sales Drawing

This document was generated on 08/27/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION