

PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION

**Part Number:** [53047-0210](#)  
**Status:** **Active**  
**Overview:** [PicoBlade™ Connector System](#)  
**Description:** 1.25mm Pitch PicoBlade™ Wire-to-Board Header, Vertical, with Friction Lock, 2 Circuits

**Documents:**  
[3D Model](#)  
[Drawing \(PDF\)](#)  
[Product Specification PS-51021-010 \(PDF\)](#)  
[Packaging Specification SPK-53047-001 \(PDF\)](#)  
[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E29179

**General**

Product Family PCB Headers  
Series [53047](#)  
Application Signal, Wire-to-Board  
Overview [PicoBlade™ Connector System](#)  
Product Name PicoBlade™  
UPC 800753566224

**Physical**

Breakaway No  
Circuits (Loaded) 2  
Circuits (maximum) 2  
Durability (mating cycles max) 30  
First Mate / Last Break No  
Flammability 94V-0  
Glow-Wire Compliant No  
Guide to Mating Part No  
Keying to Mating Part None  
Lock to Mating Part Yes  
Mated Height 5.20mm  
Material - Plating Mating Tin  
Material - Plating Termination Tin  
Net Weight 57.800/mg  
Number of Rows 1  
Orientation Vertical  
PC Tail Length 2.30mm  
PCB Locator No  
PCB Retention None  
PCB Thickness - Recommended 0.80mm  
Packaging Type Tray  
Pitch - Mating Interface 1.25mm  
Polarized to PCB No  
Shrouded Fully  
Stackable No  
Surface Mount Compatible (SMC) No  
Temperature Range - Operating -40°C to +85°C  
Termination Interface: Style Through Hole

**Electrical**

Current - Maximum per Contact 1A  
Voltage - Maximum 125V

**Material Info**




image - Reference only

Series

**EU RoHS**  
**ELV and RoHS**  
**Compliant**  
**REACH SVHC**  
**Contains SVHC: No**  
**Low-Halogen Status**  
**Not Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**  
Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
For a multiple part number RoHS Certificate of Compliance, [click here](#)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**  
[53047Series](#)

**Mates With**  
[51021](#) PicoBlade™ Wire-to-Wire

**Reference - Drawing Numbers**

Packaging Specification  
Product Specification

SPK-53047-001  
PS-51021-010, RPS-51021-007, RPS-51021-011,  
RPS-51021-041, RPS-51021-059, RPS-51021-060,  
RPS-51021-071, RPS-51021-089, RPS-51021-104  
SD-53047-\*\*10

Sales Drawing

This document was generated on 08/27/2014

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**