

## DisplayPort™ 1.2 to VGA Adapter Converter – DP to VGA – 1920x1200

StarTech ID: DP2VGA3



The DP2VGA3 DisplayPort 1.2 to VGA adapter lets you connect your DisplayPort-equipped desktop or laptop computer to a VGA monitor or projector, eliminating the expense of upgrading to a DisplayPort 1.2-capable display.

The DP to VGA adapter is fully compliant with the DisplayPort 1.2 revision, ensuring compatibility with newer DisplayPort enabled computer systems. The DisplayPort 1.2 adapter is also backward compatible with older DisplayPort revisions, ensuring this adapter will work with your DisplayPort computer. Plus, with support for resolutions up to 1920x1200 / 1080p you can convert your DisplayPort video source to work with your VGA projector or display without sacrificing video quality.

For a hassle-free setup the DisplayPort adapter allows for plug and play installation with no software or drivers required.

The DP2VGA3 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Applications

- Extend your desktop to a secondary display, by connecting a VGA monitor to your DisplayPort port
- Connect your DisplayPort computer to a VGA projector
- Carry the adapter with you while travelling to ensure your laptop is compatible with VGA displays in BYOD applications

### Features

- Fully compliant with DisplayPort 1.2 revision
- No software or drivers required
- Compact and lightweight design
- Supports video resolution up to 1920x1200 / 1080p

### Technical Specifications

|                            |   |
|----------------------------|---|
| Warranty                   | 2 Years                                     |
| Converter Type             | Active                                      |
| Adapter Style              | Adapter                                     |
| Audio                      | No  |
| Connector A                | 1 - DisplayPort (20 pin) Male               |
| Connector B                | 1 - VGA (15 pin; High Density D-Sub) Female |
| Maximum Analog Resolutions | 1920x1200                                   |
| Wide Screen Supported      | Yes   |
| Color                      | Black                                       |
| Enclosure Type             | Plastic                                     |
| Cable Length               | 100 mm [3.9 in]                             |
| Product Length             | 230 mm [9.1 in]                             |
| Product Width              | 37 mm [1.5 in]                              |
| Product Height             | 14 mm [0.6 in]                              |
| Product Weight             | 30 g [1.1 oz]                               |
| Operating Temperature      | 0°C to 60°C (32°F to 140°F)                 |
| Storage Temperature        | 0°C to 70°C (32°F to 158°F)                 |
| Humidity                   | 40%-85%RH                                   |
| Shipping (Package) Weight  | 40 g [1.4 oz]                               |
| Included in Package        | 1 - DisplayPort to VGA Adapter              |

### Certifications, Reports and Compatibility

