

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [19038-0001](#)
Status: **Active**
Overview: [Snap Plugs and Receptacles](#)
Description: InsulKrimp™ Snap Plug Receptacle, for 18-22 AWG Wire, PVC, Fits Male Plug Diameter 3.96mm

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-19902-013 \(PDF\)](#)
[Product Specification PS-19902-011 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E152602

General

Product Family Quick Disconnects
 Series [19038](#)
 Comments Fits Male Plug size 3.96mm
 Crimp Quality Equipment Yes
 Insulated No
 MolexKits Yes
 Overview [Snap Plugs and Receptacles](#)
 Product Name InsulKrimp™
 Type Snap Receptacle
 UPC 800753048621

Physical

Barrel Type Closed
 Color - Resin Red
 Flammability 94V-0
 Gender Female
 Glow-Wire Compliant No
 Insulation PVC
 Lock to Mating Part None
 Material - Metal Brass
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Material - Resin PVC
 Net Weight 1.041/g
 Orientation Straight
 Packaging Type Bag
 Plating min - Mating 4.064µm
 Plating min - Termination 4.064µm
 Tab Thickness N/A
 Tab Width N/A
 Termination Interface: Style Crimp or Compression
 Wire Insulation Diameter 3.25mm max.
 Wire Size AWG 18, 20, 22
 Wire Size mm² 0.25 - 1.50


Electrical

Voltage - Maximum 600V

Material Info

Old Part Number BRA-2156

Reference - Drawing Numbers



EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19038Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Crimp Head for the AT-200™ Pneumatic Hand Tool	0640052300
Hand Crimp Tool	0640012300

This document was generated on 09/03/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION