


# UNIVERSAL ENCLOSURES

## 2000 Series General Purpose ABS Cases

The most comprehensive, competitive range of general purpose electronic enclosures for universal applications.

- Polished external surfaces
- Integral card guides accept 1.6mm PCBs
- Low draught angle for mounting control elements on side walls
- Excellent characteristics for milling, drilling and cutting
- Lid mounted by four M3 machine screws into brass inserts in base
- PCB Adaptors (included) for horizontal mounting of PCBs



### 2000 Standard Lid




Extensive range of electronic enclosures with solid ABS lid, designed for a broad range of applications.

- Lid and Base moulded in ABS
- Lid mounted by four M3 machine screws
- Brass inserts in base for repetitive removal of the lid
- Polished finish for ease of cleaning
- Excellent properties for machining
- Integral mounting guides to accept 1.6mm PCB's
- PCB Adaptors (included) for horizontal PCB mounting

#### SPECIFICATION

|                        |                                                                                               |
|------------------------|-----------------------------------------------------------------------------------------------|
| Materials              | Lid & base high impact ABS                                                                    |
| Operating Temperature  | Resistant to temperatures of up to 85°C                                                       |
| Protection class       | IP54                                                                                          |
| Standard colours       | Grey(GY), Black(BK), Ivory(WH)                                                                |
| Standard unit includes | Combination of colours, flame retardant<br>Base & lid<br>4x M3 machine screws<br>PCB adaptors |

| GREY             | BLACK              | IVORY            | LENGTH | WIDTH | HEIGHT |
|------------------|--------------------|------------------|--------|-------|--------|
| BIM2008/8-GY/GY  | BIM2008/18-BLK/BLK | BIM2008/18-WH/WH | 55mm   | 55mm  | 42mm   |
| BIM2000/10-GY/GY | BIM2000/10-BLK/BLK | BIM2000/10-WH/WH | 75mm   | 50mm  | 27mm   |
| BIM2001/11-GY/GY | BIM2001/11-BLK/BLK | BIM2001/11-WH/WH | 85mm   | 56mm  | 39mm   |
| BIM2002/12-GY/GY | BIM2002/2-BLK/BLK  | BIM2002/12-WH/WH | 100mm  | 50mm  | 25mm   |
| BIM2003/13-GY/GY | BIM2003/13-BLK/BLK | BIM2003/13-WH/WH | 112mm  | 62mm  | 31mm   |
| BIM2007/17-GY    | BIM2007/17-BLK     | -                | 112mm  | 62mm  | 31mm   |
| BIM2004/14-GY/GY | BIM2004/14-BLK/BLK | BIM2004/14-WH/WH | 120mm  | 65mm  | 40mm   |
| RTM2030/30-GY    | RTM2030/30-BLK     | -                | 142mm  | 80mm  | 30mm   |
| BIM2005/5-GY/GY  | BIM2005/15-BLK/BLK | BIM2005/15-WH    | 150mm  | 80mm  | 50mm   |
| BIM2006/16-GY/GY | BIM2006/16-BLK/BLK | BIM2006/16-WH/WH | 190mm  | 110mm | 60mm   |
| BIM2009/19-GY/GY | -                  | -                | 250mm  | 200mm | 64mm   |



UNIVERSAL  
ENCLOSURES

HAND  
HELD  
CASES

HEAVY  
DUTY  
ENCLOSURES

DIN  
RAIL  
BOXES

INTERFACE  
SUPPORTS

CONTROL  
STATIONS

DIECAST  
& METAL  
BOXES

DESKTOP &  
INSTRUMENT  
CASES

POTTING  
BOXES

19"  
ENCLOSURES

19"  
CABINETS

DEVELOPMENT  
BOARDS

CUSTOM  
SIZED  
ENCLOSURES

CUSTOM  
SERVICES