

# STEEL WEB STOPPERS



## STI STEEL WEB STOPPERS




Choosing the right STI Smoke Detector Protector for your application. Use one of our Steel Web Stoppers (shown here) with a plastic coated, 9 gauge steel rod or stainless steel construction if...

- The risk of abuse to smoke detectors is severe
- Smoke detectors are located in vulnerable areas where vandalism or accidental damage is frequent
- Variety of sizes within the range can fit a wider choice of devices
- Stainless steel construction is required
- Plastic coated version is required for indoor or outdoor use

Use our Polycarbonate Detector Stopper (page 11) made from tough polycarbonate if...


- The risk of physical abuse to smoke detectors is severe
- It's advisable to lessen the chances of self harm in correctional facilities and mental hospitals (slots are too small for even a pencil to be passed through them)
- Translucent unit more aesthetically appealing
- Range of colours available to compliment your building interior

## MODELS AVAILABLE

FLUSH MOUNT	MAX. INTERNAL DIAMETER	MIN. INTERNAL DIAMETER	INTERNAL DEPTH	
STI 9601	210mm (8.25")	150mm (6")	70mm (2.75")	STI 9604
STI 9604	175mm (6.88")	125mm (5")	75mm (2.95")	
STI 9606	175mm (6.88")	110mm (4.3")	95mm (3.74")	STI 9604-SS
STI 9609	215mm (8.5")	78mm (3")	124mm (4.88")	
STI 9713	174mm (6.87")	50mm (1.97")	63mm (2.5")	STI 9605
SURFACE MOUNT	MAX. INTERNAL DIAMETER	MIN. INTERNAL DIAMETER	INTERNAL DEPTH	
STI 9602	215mm (8.5")	155mm (6")	108mm (4.25")	
STI 9605	180mm (7")	100mm (4")	115mm (4.5")	
STI 9610	214mm (8.4")	85mm (3")	145mm (5.7")	
STI 9712	174mm (6.87")	50mm (1.97")	115mm (4.5")	

**Options:** For a stainless steel finish add -SS  
**Example:** STI 9604-SS = Steel Web Stopper, flush mounted with stainless steel finish  
**NB:** STI 9604, STI 9605 & STI 9609 only models available in a stainless steel finish

▼ Steel Web Stopper dimensions and technical information (STI 9601, STI 9602, STI 9604, STI 9604-SS, STI 9605, STI 9605-SS, STI 9606, STI 9609, STI 9609-SS, STI 9610, STI 9713 & STI 9712)



VISIT [WWW.STI-EUROPE.COM](http://WWW.STI-EUROPE.COM) FOR ALL LATEST PRODUCT NEWS