

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

15-31-1092

Status:

Active

Description:

4.80mm Pitch Wire-to-Wire Receptacle Housing, 9 Circuits

Documents:

|                                                         |                                                         |
|---------------------------------------------------------|---------------------------------------------------------|
| <a href="#">Drawing (PDF)</a>                           | <a href="#">Product Specification PS-5025-003 (PDF)</a> |
| <a href="#">Product Specification PS-5025-001 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>    |
| <a href="#">Product Specification PS-5025-002 (PDF)</a> |                                                         |

Agency Certification

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

General

|                |                     |
|----------------|---------------------|
| Product Family | Crimp Housings      |
| Series         | 5025                |
| Application    | Power, Wire-to-Wire |
| Product Name   | N/A                 |
| UPC            | 800753604179        |

Physical

|                               |                 |
|-------------------------------|-----------------|
| Circuits (maximum)            | 9               |
| Color - Resin                 | Natural         |
| Flammability                  | 94V-2           |
| Gender                        | Female          |
| Glow-Wire Compliant           | No              |
| Material - Resin              | Nylon           |
| Net Weight                    | 3193.400/mg     |
| Number of Rows                | 3               |
| Packaging Type                | Bag             |
| Panel Mount                   | No              |
| Pitch - Mating Interface      | 4.80mm          |
| Pitch - Termination Interface | 4.80mm          |
| Temperature Range - Operating | -40°C to +105°C |

Material Info

|                 |           |
|-----------------|-----------|
| Old Part Number | 5025-09R1 |
|-----------------|-----------|

Reference - Drawing Numbers

|                       |                                                     |
|-----------------------|-----------------------------------------------------|
| Product Specification | PS-5025-001, PS-5025-002, PS-5025-003, RPS-5025-004 |
| Sales Drawing         | SD-5025-09R1                                        |

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

5025Series

Mates With

5025 Plug

Use With

5005

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION