

TLS 2200® Asset Tracking Materials

www.BradyID.com/tls2200



TLS 2200® Asset Tracking Materials:

B-483 Polyester Material

Color: White Finish: Gloss

White polyester with glossy finish and aggressive adhesive specifically designed for powder coated surfaces.

Performance Attributes:



Figure 28




Figure 29




Figure 33




Figure 46

(Includes black border)




Figure 72

(Includes pre-printed header)



Diagram	Part Number	B-#	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Labels Per Row	Labels Per Pkg	Rec. Ribbon
Fig. 33	PTL-101-483	B-483	Polyester	White	0.250 (6.4)	50 ft. (15.2 m)	1	1 Roll Cont.	R6010
Fig. 33	PTL-8-483	B-483	Polyester	White	0.500 (12.7)	50 ft. (15.2 m)	1	1 Roll Cont.	R6010
Fig. 29	PTL-16-483	B-483	Polyester	White	1.000 (25.4)	0.375 (9.5)	1	500	R6010
Fig. 29	PTL-17-483	B-483	Polyester	White	1.000 (25.4)	0.500 (12.7)	1	500	R6010
Fig. 29	PTL-19-483	B-483	Polyester	White	1.000 (25.4)	1.000 (25.4)	1	250	R6010
Fig. 33	PTL-42-483	B-483	Polyester	White	1.000 (25.4)	50 ft. (15.2 m)	1	1 Roll Cont.	R6010
Fig. 46	PTL-24-483-BK	B-483	Polyester	Black border	1.130 (28.7)	0.500 (12.7)	1	500	R6010
Fig. 33	PTL-100-483	B-483	Polyester	White	1.300 (33.0)	50 ft. (15.2 m)	1	1 Roll Cont.	R6010
Fig. 29	PTL-65-483	B-483	Polyester	White	1.375 (34.9)	1.000 (25.4)	1	250	R6010
Fig. 29	PTL-29-483	B-483	Polyester	White	1.500 (38.1)	0.500 (12.7)	1	500	R6010
Fig. 29	PTL-30-483	B-483	Polyester	White	1.500 (38.1)	0.750 (19.1)	1	250	R6010
Fig. 29	PTL-31-483	B-483	Polyester	White	1.500 (38.1)	1.000 (25.4)	1	250	R6010
Fig. 29	PTL-32-483	B-483	Polyester	White	1.500 (38.1)	1.500 (38.1)	1	250	R6010
Fig. 33	PTL-43-483	B-483	Polyester	White	1.900 (48.3)	50 ft. (15.2 m)	1	1 Roll Cont.	R6010
Fig. 29	PTL-20-483	B-483	Polyester	White	2.000 (50.8)	1.000 (25.4)	1	100	R6010
Fig. 28	PTL-61-483	B-483	Polyester	White	2.000 (50.8)	0.500 (12.7)	1	100	R6010
Fig. 29	PTL-37-483	B-483	Polyester	White	3.000 (76.2)	1.900 (48.3)	1	100	R6010
Fig. 72	PTL-37-483-DANGER	B-483	Polyester	Red on White	3.000 (76.2)	1.900 (48.3)	1	100	R6010
Fig. 72	PTL-37-483-WARNING	B-483	Polyester	Orange/Black on White	3.000 (76.2)	1.900 (48.3)	1	100	R6010
Fig. 29	PTL-23-483	B-483	Polyester	White	4.000 (101.6)	1.000 (25.4)	1	100	R6010
Fig. 72	PTL-38-483-DANGER	B-483	Polyester	Red on White	4.000 (101.6)	1.900 (48.3)	1	100	R6010
Fig. 72	PTL-38-483-WARNING	483	Polyester	Orange/Black on White	4.000 (101.6)	1.900 (48.3)	1	100	R6010



TLS 2200® Asset Tracking Materials:

B-486 Polyester Material

Color: Silver Metallic Finish: Matte

Metallized polyester material designed for high adhesion to textured metals, powder coated surfaces and low surface energy plastics. Withstands numerous solvents and variable temps.

Performance Attributes:




Figure 29




Figure 46
(Includes black border)



Diagram	Part Number	B-#	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Labels Per Row	Labels Per Pkg	Rec. Ribbon
Fig. 29	PTL-16-486	B-486	Polyester	Silver	1.000 (25.4)	0.375 (9.5)	1	500	R4310
Fig. 29	PTL-17-486	B-486	Polyester	Silver	1.000 (25.4)	0.500 (12.7)	1	500	R4310
Fig. 29	PTL-19-486	B-486	Polyester	Silver	1.000 (25.4)	1.000 (25.4)	1	250	R4310
Fig. 46	PTL-24-486-BK	B-486	Polyester	Silver/Black Border	1.130 (28.7)	0.500 (12.7)	1	500	R4310
Fig. 29	PTL-29-486	B-486	Polyester	Silver	1.500 (38.1)	0.500 (12.7)	1	500	R4310
Fig. 29	PTL-30-486	B-486	Polyester	Silver	1.500 (38.1)	0.750 (19.1)	1	250	R4310
Fig. 29	PTL-31-486	B-486	Polyester	Silver	1.500 (38.1)	1.000 (25.4)	1	250	R4310
Fig. 29	PTL-32-486	B-486	Polyester	Silver	1.500 (38.1)	1.500 (38.1)	1	250	R4310
Fig. 29	PTL-20-486	B-486	Polyester	Silver	2.000 (50.8)	1.000 (25.4)	1	100	R4310
Fig. 29	PTL-37-486	B-486	Polyester	Silver	3.000 (76.2)	1.900 (48.3)	1	100	R4310
Fig. 29	PTL-38-486	B-486	Polyester	Silver	4.000 (101.6)	1.900 (48.3)	1	100	R6010
Fig. 29	PTL-38-486	B-486	Polyester	Silver	4.000 (101.6)	1.900 (48.3)	1	100	R4310

View the Material Brands & Attributes Guide on page 4.

TLS2200® Printer Ribbons on page 67.

Full Material Properties on page 187.

1-888-272-3946 | www.BradyID.com