

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0918038417](#)  
**Status:** **Obsolete**  
**Description:** 0.50mm (.020") Pitch LaneLink™ I/O Jack Screw Receptacle, 4 Lane, SAS, SATA, Fibre Channel, 8 Circuits, Tape and Reel, Rear Mounts, 4 Solder Posts, Metal Gasket

**Documents:**  
[Drawing \(PDF\)](#)

**General**


Product Family	I/O Connectors
Series	<a href="#">91803</a>
Application	Wire-to-Board
Comments	Loctite 270 or 275 to be used when assembling solder posts Metal Gasket
Component Type	Receptacle
Product Name	InfiniBand*, LaneLink™
Type	N/A

**Physical**

Boot Color	N/A
Circuits (Loaded)	25
Circuits (maximum)	25
Circuits Detail	8 Differential Pair
Color - Resin	Black
Durability (mating cycles max)	250
Gender	Plug
Lock to Mating Part	Yes
Material - Metal	Beryllium Copper, Brass, Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Number of Rows	2
Orientation	Right Angle
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm (.063"), 2.10mm (.083")
Packaging Type	Embossed Tape on Reel
Panel Mount	Yes
Pitch - Mating Interface	1.50mm (.059")
Pitch - Termination Interface	1.50mm (.059")
Plating min - Mating	0.102µm (4µ")
Plating min - Termination	3.048µm (120µ")
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-20°C to +60°C
Termination Interface: Style	Surface Mount
Waterproof / Dustproof	Yes
Wire Size AWG	N/A

**Electrical**

Current - Maximum per Contact	0.5A
Shield Type	EMI Gasket
Shielded	Yes
Voltage - Maximum	30V AC



*image - Reference only*

**EU RoHS**

**ELV and RoHS  
Compliant**

**REACH SVHC**

Not Reviewed

**Low-Halogen Status**

Not Reviewed

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[91803Series](#)

**Mates With**

[92903](#) , [91659](#)

**Use With**

[91789-0001](#)

## Material Info

### Reference - Drawing Numbers

Application Specification	AS-91803-001
Packaging Specification	PK-91629-003, PK-91803-001
Product Specification	PS-91525-001
Sales Drawing	SD-91803-003

\* InfiniBand is a trademark of the InfiniBand Trade Association

This document was generated on 03/11/2011

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**