



Grips Glow in the Dark

to help find your tools.

Lasts up to 30 minutes!*

Grips charge
in natural and artificial lighting.

Glow in the dark grips
to easily locate your tool in dark or low lit areas.



**Side-Cutting Pliers
High-Leverage**

D2000-9NEGLW

- Cuts ACSR, screws, nails, and most hardened wire.
- High-leverage design. Rivet is closer to the cutting edge for 46% greater cutting and gripping power than other plier designs.
- Sure-gripping cross-hatched knurled jaws.



**Diagonal-Cutting Pliers
High-Leverage**

D2000-28GLW

- Cuts ACSR, screws, nails, and most hardened wire.
- High-leverage design. Rivet is closer to the cutting edge for 36% greater cutting power than other plier designs.
- Short jaws and beveled cutting edges permit close cutting of wire, nails, and most hardened wire.



**Wire
Stripper/Cutter**

11054GLW

- Cuts, strips and loops 8-16 AWG Solid and 10-18 AWG Stranded wire.
- Strong-gripping serrated nose for easy bending, shaping, and pulling of wire.
- Cleanly shears 6-32 and 8-32 screws.
- Handy closure lock for convenient storage.

Cat. No.	UPC# 0-92644+	Overall Length	Strips and Cuts	Jaw Length	Jaw Width	Jaw Thickness	Handle Finish	Weight (lbs.)
D2000-9NEGLW	38003-7	9-3/8" (238 mm)	N/A	1-19/32" (41 mm)	1-1/4" (32 mm)	5/8" (16 mm)	hi-visibility	1.09
D2000-28GLW	38004-4	8-1/16" (205 mm)	N/A	13/16" (21 mm)	1-3/16" (30 mm)	7/16" (11 mm)	hi-visibility	.67
11054GLW	34115-1	7-1/8" (181 mm)	8 – 16 AWG solid (8.4 mm ² – 1.3 mm ²) & 10 – 18 AWG stranded (5.3 mm ² – .82 mm ²)	N/A	N/A	N/A	hi-visibility	.34

*NOTE: Glow time and intensity may vary if charged in low light.
Clean grips regularly to maintain glow brightness.

Available in an interactive display

Cat. No.	Description	Qty. 4 of Each
96356	12 pc. Interactive Counter Display	D2000-9NEGLW, D2000-28GLW and 11054GLW



KLEIN TOOLS
For Professionals... Since 1857®

www.kleintools.com



© 2013 Klein Tools, Inc.
Lincolnshire, IL. 60069-1418
96350

Hi-Visibility Tools