

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

15-97-5101

Status:

Active

Overview:

Mini-Fit® TPA Plugs and Receptacles

Description:

Mini-Fit® TPA Receptacle Housing, 4.20mm Pitch, Dual Row with Secondary Terminal Retention, 10 Circuits



image - Reference only

Series

Documents:

- [3D Model](#)
- [Drawing \(PDF\)](#)
- [Product Specification PS-45750-001 \(PDF\)](#)
- [Product Specification PS-5556-003 \(PDF\)](#)
- [Packaging Specification PK-30067-001 \(PDF\)](#)
- [Test Summary TS-30067-001 \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA	LR19980
TUV	R72081037
UL	E29179

General

Product Family	Crimp Housings
Series	30067
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Current = 13A max. per circuit when header is mated to a receptacle loaded with 45750 series terminals crimped to 16 AWG wire. . See Molex product specification PS-45750-001 for additional current derating information.. Connector Position Assurance
Overview	Mini-Fit® TPA Plugs and Receptacles
Product Name	Mini-Fit® TPA
UPC	800754202206

Physical

Breakaway	No
Circuits (maximum)	10
Color - Resin	Black
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	3.027/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.20mm
Stackable	No
Temperature Range - Operating	-40°C to +105°C

Electrical

Current - Maximum per Contact	13A
-------------------------------	-----

Material Info

Old Part Number	30067-10A2
-----------------	------------

Reference - Drawing Numbers

Packaging Specification	PK-30067-001
Product Specification	PS-45750-001, PS-5556-003

EU RoHS

ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

30067Series

Mates With

Plug 30068 , Straight Header 30069 , Right Angle Header 30070 , 44483

Use With

30072 4.20mm Pitch Mini-Fit® TPA Receptacle Housing, 45750 Mini-Fit® Plus HCS Crimp Terminal

This document was generated on 10/21/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION