



# iMedia® Screencast™ 2.2

1080P HIGH-DEFINITION DIGITAL SIGNAGE DISPLAY ADAPTOR  
Model: AV25049



- Introduction**  
About AEI
- DigiSender**  
Video Senders
- DigiSenderTV**  
SuperSmartTV Upgrades
- iMedia**  
Android Devices
- AEI Security**  
Alarm Systems & CCTV
- Remote Automation**  
Gadgets for the Home

- iMedia Blaze**  
Tablets
- iMedia Atom**  
Smartphones
- iMedia Eclipse**  
Netbooks
- iMedia Gamer**  
Consoles & Gamepads
- iMedia Interactive**  
Digital Signage
- Accessories

- Screencast2.2**  
DGIMD132

**AEI Security & Communications Ltd.**  
Weslake Industrial Park,  
Rye Harbour Road, Rye,  
East Sussex, TN31 7TE

**Web:**  
www.digisender.net

**Email:**  
sales@aei.eu

**Telephone:**  
02071 931 413

© AEI Security & Communications Limited.  
All rights reserved.



The iMedia Screencast2.2 adaptor converts your TV into a wireless display. By simply installing the adaptor into a spare HDMI port on your TV you are then able to start Wireless Display on your Android device, or Airplay on your iOS device and see exactly what appears on your mobile device on your TV. There is no complicated setting up or special app download required. It is also compatible with Windows 8 and above for that all-important big screen presentation from your laptop.

It is the most flexible way to share your mobile content on your TV because it works with any app you have loaded on your mobile device or laptop. No matter how you gain access to your media, from the internet or built in memory you can sit back and enjoy movies on the TV or even display and share your photos in stunning and vibrant colours for all to see.

If you are worried about compatibility, then worry not, because the Scceencast2.2 adaptor also works with DLNA apps. The DLNA service allows thousands of various apps available for all devices to share movies and music in the same way but simply transferring their display to the big screen only.

## Features

- Transmit your Phone or Tablet Screen to your TV.
- FULL HD 1080p Output.
- Crystal Clear Dual-Channel Digital Audio (Stereo).
- Works with Miracast, DLNA and UPnP protocols.
- Supports Android Phones, Tablets and Set-top Boxes via Miracast and DLNA.
- Supports Apple Phones, Tablets, Mac Books and Macs via Airplay and DLNA.
- Supports Windows 8 Laptops, PC's, Phones and Tablets via Miracast and DLNA, including 'Extended Display Mode'.
- Discreet Stick Style Design.
- Powered via your TV's USB Port or via USB Mains Adaptor.

## Specifications

- HD Video Decoder: 1080p @ 60fps
- Wi-Fi: 802.11 b/g/n
- Connections: 1x HDMI, 1x Micro USB
- Miracast: Most devices running Android 4.2 and above
- Airplay: Most devices running iO7 and above
- UPnP/DLNA: All UPnP & DLNA compatible devices
- Power: USB or 5V 1A USB Mains adaptor
- Dimensions: 75 x 33 x 9.3mm

## Kit Contents

- 1x AV25049 Adaptor
- 1x HDMI Extension Cable
- 1x USB Cable
- 1x Charger
- 1x Quick Guide