

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [02-09-8104](#)  
**Status:** **Active**  
**Overview:** Standard .093" Pin and Socket Connectors  
**Description:** 2.36mm Diameter, Standard .093" Pin and Socket Crimp Grounding Terminal, Series 1973, Male, with Tin (Sn) Plated Brass Contact, 18-22 AWG, Bag

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-02-09 \(PDF\)](#)

**General**

Product Family	Crimp Terminals
Series	1973
Application	Power
Comments	Grounding Pin
Crimp Quality Equipment	Yes
Overview	<a href="#">Standard .093" Pin and Socket Connectors</a>
Packaging Alternative	<a href="#">02-09-8103 (Reel)</a>
Product Name	Standard .093"
UPC	800754230476

**Physical**


Durability (mating cycles max)	25
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.343/g
Packaging Type	Bag
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.52-3.05mm
Wire Size AWG	18, 20, 22
Wire Size mm²	N/A

**Material Info**

Old Part Number 1973-A(P913)L

**Reference - Drawing Numbers**

Product Specification PS-02-09  
 Sales Drawing SD-1973-\*



**EU RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC Contains SVHC: No**  
**Low-Halogen Status Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

1973Series

**Use With**

1619 Plug or Receptacle Housing, 1545 Plug or Receptacle Housing, 1396 Plug or Receptacle Housing, 1490 Plug or Receptacle Housing, 2629 Plug or Receptacle Crimp Housings, 1261 Plug or Receptacle Housing, 1292 Plug or Recept

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Hand Crimp Tool	<a href="#">0638191200</a>
Extractor Tool for .093 and HCS-125 Product Series	<a href="#">0638240200</a>
Insertion Tool	<a href="#">0011020003</a>

This document was generated on 10/14/2014

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**