

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [50058-8100](#)
Status: **Active**
Overview: [PicoBlade™ Connector System](#)
Description: 1.25mm Pitch PicoBlade™ Crimp Terminal, Female, 28-32 AWG, Bag

Documents:

3D Model	Product Specification PS-51021-022 (PDF)
Drawing (PDF)	Product Specification PS-51021-023 (PDF)
Product Specification PS-51021-001 (PDF)	Product Specification PS-51021-024 (PDF)
Product Specification PS-51021-002 (PDF)	Product Specification PS-51021-026 (PDF)
Product Specification PS-51021-009 (PDF)	Product Specification PS-51021-027 (PDF)
Product Specification PS-51021-010 (PDF)	Product Specification PS-51021-028 (PDF)
Product Specification PS-51021-011 (PDF)	RoHS Certificate of Compliance (PDF)




image - Reference only

General

Product Family	Crimp Terminals
Series	50058
Application	Signal
Crimp Quality Equipment	Yes
Overview	PicoBlade™ Connector System
Packaging Alternative	50058-8000 (Reel)
Product Name	PicoBlade™
UPC	800753719620

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	12.600/mg
Packaging Type	Bag
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.50-1.00mm
Wire Size AWG	28, 30, 32
Wire Size mm²	N/A

Material Info

Reference - Drawing Numbers

Product Specification [PS-51021-001](#), [PS-51021-002](#), [PS-51021-009](#), [PS-51021-010](#), [PS-51021-011](#), [PS-51021-022](#), [PS-51021-023](#), [PS-51021-024](#), [PS-51021-026](#), [PS-51021-027](#), [PS-51021-028](#), [RPS-501576-001](#), [RPS-51021-001](#), [RPS-51021-002](#), [RPS-51021-003](#), [RPS-51021-004](#), [RPS-51021-006](#), [RPS-51021-007](#), [RPS-51021-008](#), [RPS-51021-009](#), [RPS-51021-010](#), [RPS-51021-011](#), [RPS-51021-013](#), [RPS-51021-014](#), [RPS-51021-015](#), [RPS-51021-016](#), [RPS-51021-017](#), [RPS-51021-018](#), [RPS-51021-019](#), [RPS-51021-020](#), [RPS-51021-021](#), [RPS-51021-022](#), [RPS-51021-023](#), [RPS-51021-024](#), [RPS-51021-025](#), [RPS-51021-026](#), [RPS-51021-027](#), [RPS-51021-028](#), [RPS-51021-029](#), [RPS-51021-030](#), [RPS-51021-031](#), [RPS-51021-032](#), [RPS-51021-033](#), [RPS-51021-037](#), [RPS-51021-038](#),

EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[50058Series](#)

Mates With

[50125 Crimp Terminal 26-28 AWG](#), [50133 Crimp Terminal 28-32 AWG](#)

Use With

[51021 Housing](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool for 1.25mm Pitch Crimp Terminals, 26-32 AWG Wire	0638190300
Hand Crimp Tool for 1.25mm Pitch Crimp	0638190400

RPS-51021-039, RPS-51021-040, RPS-51021-041,
RPS-51021-042, RPS-51021-043, RPS-51021-044,
RPS-51021-045, RPS-51021-046, RPS-51021-047,
RPS-51021-048, RPS-51021-050, RPS-51021-051,
RPS-51021-052, RPS-51021-053, RPS-51021-054,
RPS-51021-055, RPS-51021-056, RPS-51021-057,
RPS-51021-058, RPS-51021-059, RPS-51021-060,
RPS-51021-061, RPS-51021-062, RPS-51021-063,
RPS-51021-064, RPS-51021-065, RPS-51021-066,
RPS-51021-067, RPS-51021-068, RPS-51021-071,
RPS-51021-072, RPS-51021-073, RPS-51021-074,
RPS-51021-076, RPS-51021-077, RPS-51021-078,
RPS-51021-079, RPS-51021-080, RPS-51021-081,
RPS-51021-083, RPS-51021-084, RPS-51021-085,
RPS-51021-086, RPS-51021-089, RPS-51021-091,
RPS-51021-092, RPS-51021-096, RPS-51021-097,
RPS-51021-101, RPS-51021-102, RPS-51021-103,
RPS-51021-105, RPS-51021-106, RPS-51021-107,
RPS-51021-108, RPS-51021-110, RPS-51021-112,
RPS-51021-117, RPS-51021-118, RPS-51021-121,
RPS-51021-122, RPS-53398-002, RPS-53398-037,
RPS-53398-038
SD-50058-8*00

Sales Drawing

Terminals, 26-32 AWG Wire Extraction Tool	<u>0011030043</u>
Japan	
Description	Product #
Hand Crimp Tool	<u>0570685000</u>
Extraction Tool	<u>0570726000</u>

This document was generated on 10/14/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION