Punch Down Tools


- Insert and cut cable terminations effortlessly
- Adjustable high/low actuation setting accommodates termination requirements
- Turn-Lock™ Style blade holding design
- Impact-absorbing cushioned grip reduces operator stress for high volume installers



35-492



Impact Turn-Lock™ Punch Down Tools	Cat. No.
Punchmaster™ II Punch Down Tool w/full 110 & 66 blades	35-485
Non-Impact Turn-Lock™ Punch Down Tools	Cat. No.
Punch Down Tool w/110 blade	35-492
Economy Punch Down Tool	Cat. No.
Non-impact Tool w/permanent non-cut blade	35-185
_	



Removable Blades*	Cat. No.
110 Turn-Lock™ blade	35-495
66 Turn-Lock™ blade	35-497
110/66 combo blade w/cutting edges	35-407
Krone® blade	35-478
Bix® blade	35-479

*Not applicable for Economy Punch Down tool.

Bix® is a registered trademark of Nortel. Krone® is a registered trademark of Krone, Inc.

Ratchet Telemaster™

- · Heavy-duty steel frame
- For paired conductors
- Ratchet version of our Telemaster[™] Tool for RJ-45 and RJ-11 modular plugs
- Repeatable crimp action for consistent, high quality connections

Description	Cat. No.
Ratchet Telemaster™	30-696
Replacement Cut & Strip Blade Set for 30-696	LA-4102

Telemaster™ Telephone Tools

- For paired conductors
 - Multi-function telephone tool cuts, strips and crimps for easy one-tool application
- Steel frame for long-term durability. (Crimps primary modular plug strain relief only)

Description	Kit Cat. No.	Tool Only Cat. No.
Tool for RJ-11 (1, 2, 3 pair) and RJ-45 (4 pair) Plugs	33-700*	30-496
Tool for RJ-22 (handset) and RJ-11 (1, 2, 3 pair)	N/A	30-499
Replacement Cut and Strip Blade Set for Telemaster TM	N/A	LB-1747

*Kit includes 10 each, RJ-45 8P8C, RJ-11 6P6C and RJ-11 6P4C modular plugs

Data/Voice Crimp Tool Kit

- Compact design is 2/3 the size of traditional crimpers
- Fixed RJ-45 and RJ-11 crimp cavities
- One tool assembly process – cut, strip and crimp connectors on to CAT 3/5e/6 cables
- Black oxide coated steel core with spring loaded handle and locking feature

Description	Cat. No.
Data/Voice Crimp Tool Kit includes ten RJ-11and ten RJ-45 connectors	33-396

of

UTP/STP/Coaxial Cable Strippers

 Adjustable blades can be set for any depth to help ensure nick-free stripping and slitting of cables.





Description	Typical RG Cables	Cat. No.
Coaxial Cable Stripper, up to 1/8 in. (3.2mm) O.D	RG-174, RG-187	45-162 (Gray)
Coaxial Cable Stripper, 1/8 in. (3.2mm) to 7/32 in. (5.556mm) O.D.	Mini Coax RG-58,CB	45-163 (Blue)
Coaxial Cable Stripper, 1/4 in. (6.4mm) to 9/16 in. (14.3mm) O.D.	RG-11, RG-8	45-164 (Blue)
Cable Stripper, 3/16 in. (4.8mm) to 5/16 in. (8mm) O.D.	RG-59/6, UTP Cable	45-165 (Black)
UTP/STP Ringer Stripper, one blade	UTP/STP	45-168 (Black)
Replacement Blade Set* for 45-162, 45-163, 45-165	_	L-9225
Replacement Blade Set* for 45-164	_	L-9226

^{*}A set of blades consists of three straight blades and one round blade.

Cyclops[®] Data Cable Stripper

 Fast, easy removal outer sheath insulations (PVC and Plenum types,

Description	Cat. No.
Data Cable Stripper for unshielded and shielded twisted pair cable	45-514

PrepPRO® Coax/UTP Cable Stripper

- Auto adjusting blade depth for 6/6Quad/59 coax cable
- 1/4" x 1/4" coax preparation
- · Replaceable blade cartridges
- CAT5e/6 jacket stripping
- Spring loaded for consistent cutting force

Description	Cat. No.
PrepPRO® Coax/UTP Cable Stripper	45-605