

TE P/N	TE CD	Nanonics P/N	Part Description
1589457-1	1589457	SSL005SC0DC006N	Dualobe, 1 row, LCP, 5 position, receptacle, 28 AWG solid, color coded PTFE wire, 6 inches, thread for 1.0 jackscrews.
1589457-2	1589457	SSL005SC2DC006N	Dualobe, 1 row, LCP, 5 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 6 inches, thread for 1.0 jackscrews.
1589457-3	1589457	SSL005SC3DM024N	Dualobe, 1 row, LCP, 5 position, receptacle, 32 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 24 inches, thread for 1.0 jackscrews.
1589457-4	1589457	SSL009SC0DMM03N	Dualobe, 1 row, LCP, 9 position, receptacle, 28 AWG solid, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 3 meters, thread for 1.0 jackscrews.
1589457-5	1589457	SSL009SC2DC003	Dualobe, 1 row, LCP, 9 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 3 inches.
1589457-6	1589457	SSL009SC2DC006N	Dualobe, 1 row, LCP, 9 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 6 inches, thread for 1.0 jackscrews.
1589457-7	1589457	SSL009SC2DC012	Dualobe, 1 row, LCP, 9 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 12 inches.
1589457-8	1589457	SSL009SC2DM006N	Dualobe, 1 row, LCP, 9 position, receptacle, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 6 inches, thread for 1.0 jackscrews.
1589457-9	1589457	SSL009SC2DM006N7	Dualobe, 1 row, LCP, 9 position, receptacle, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 6 inches, barrel nuts.
1-1589457-0	1589457	SSL009SC2GX006	Dualobe, 1 row, LCP, 9 position, receptacle, 30 AWG 7 strand, FEP ribbon cable, 6 inches.
1-1589457-1	1589457	SSL015SC0DMM03N	Dualobe, 1 row, LCP, 15 position, receptacle, 28 AWG solid, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 3 meters, thread for 1.0 jackscrews.
1-1589457-2	1589457	SSL015SC2DC006N	Dualobe, 1 row, LCP, 15 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 6 inches, thread for 1.0 jackscrews.
1-1589457-3	1589457	SSL015SC2DC012N	Dualobe, 1 row, LCP, 15 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 12 inches, thread for 1.0 jackscrews.
1-1589457-4	1589457	SSL015SC2DC024N	Dualobe, 1 row, LCP, 15 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 24 inches, thread for 1.0 jackscrews.
1-1589457-5	1589457	SSL025SC2DC006	Dualobe, 1 row, LCP, 25 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 6 inches.
1-1589457-6	1589457	SSL025SC2DC006N	Dualobe, 1 row, LCP, 25 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 6 inches, thread for 1.0 jackscrews.
1-1589457-7	1589457	SSL025SC2DC012N	Dualobe, 1 row, LCP, 25 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 12 inches, thread for 1.0 jackscrews.
1-1589457-8	1589457	SSL037SC2DC012N	Dualobe, 1 row, plastic, 37 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 12 inches, thread for 1.0 jackscrews.
1-1589457-9	1589457	SSM005SC2DC006N	Dualobe, 1 row, metal, 5 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 6 inches, thread for 1.0 jackscrews.
2-1589457-0	1589457	SSM005SC2DC012N	Dualobe, 1 row, metal, 5 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 12 inches, thread for 1.0 jackscrews.
2-1589457-1	1589457	SSM005SC2DC018N	Dualobe, 1 row, metal, 5 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 18 inches, thread for 1.0 jackscrews.
2-1589457-2	1589457	SSM005SC2DC040N	Dualobe, 1 row, metal, 5 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 40 inches, thread for 1.0 jackscrews.
2-1589457-3	1589457	SSM005SC2DX024HN	Dualobe, 1 row, metal, 5 position, receptacle, 30 AWG 7 strand, white PTFE wire, 24 inches, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
2-1589457-4	1589457	SSM005SC4DX012N	Dualobe, 1 row, metal, 5 position, receptacle, 34 AWG 7 strand, white PTFE wire, 12 inches, thread for 1.0 jackscrews.
2-1589457-5	1589457	SSM009SC1DC002	Dualobe, 1 row, metal, 9 position, receptacle, 30 AWG single strand, color coded PTFE wire, 2 inches.
2-1589457-6	1589457	SSM009SC2DC006HN	Dualobe, 1 row, metal, 9 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 6 inches, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
2-1589457-7	1589457	SSM009SC2DC006N	Dualobe, 1 row, metal, 9 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 6 inches, thread for 1.0 jackscrews.
2-1589457-8	1589457	SSM009SC2DC012HM	OBSOLETE
2-1589457-9	1589457	SSM009SC2DC012N	Dualobe, 1 row, metal, 9 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 12 inches, thread for 1.0 jackscrews.
3-1589457-0	1589457	SSM009SC2DC018N	Dualobe, 1 row, metal, 9 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 18 inches, thread for 1.0 jackscrews.
3-1589457-1	1589457	SSM009SC2DC024N	Dualobe, 1 row, metal, 9 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 24 inches, thread for 1.0 jackscrews.
3-1589457-2	1589457	SSM009SC2DC036N	Dualobe, 1 row, metal, 9 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 36 inches, thread for 1.0 jackscrews.
3-1589457-3	1589457	SSM009SC2DC048RN	Dualobe, 1 row, metal, 9 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 48 inches, clearance hole for 1.0 mounting screw, thread for 1.0 jackscrews.
3-1589457-4	1589457	SSM009SC2DM006N	Dualobe, 1 row, metal, 9 position, receptacle, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 6 inches, thread for 1.0 jackscrews.
3-1589457-5	1589457	SSM009SC2DM012	Dualobe, 1 row, metal, 9 position, receptacle, 30AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 12 inches.
3-1589457-6	1589457	SSM009SC2DX012N	Dualobe, 1 row, metal, 9 position, receptacle, 30 AWG 7 strand, white PTFE wire, 12 inches, thread for 1.0 jackscrews.
3-1589457-7	1589457	SSM009SC2DX018N	Dualobe, 1 row, metal, 9 position, receptacle, 30 AWG 7 strand, white PTFE wire, 18 inches, thread for 1.0 jackscrews.
3-1589457-8	1589457	SSM009SC2DX024HN	Dualobe, 1 row, metal, 9 position, receptacle, 30 AWG 7 strand, white PTFE wire, 24 inches, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
3-1589457-9	1589457	SSM009SC2DX036HN	Dualobe, 1 row, metal, 9 position, receptacle, 30 AWG 7 strand, white PTFE wire, 36 inches, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
4-1589457-0	1589457	SSM015SC0DC012N	Dualobe, 1 row, metal, 15 position, receptacle, 28 AWG solid, color coded PTFE wire, 12 inches thread for 1.0 jackscrews.
4-1589457-1	1589457	SSM015SC2DC003N	Dualobe, 1 row, metal, 15 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 3 inches thread for 1.0 jackscrews.
4-1589457-2	1589457	SSM015SC2DC006N	Dualobe, 1 row, metal, 15 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 6 inches thread for 1.0 jackscrews.
4-1589457-3	1589457	SSM015SC2DC012N	Dualobe, 1 row, metal, 15 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 12 inches, thread for 1.0 jackscrews.
4-1589457-4	1589457	SSM015SC2DC018	Dualobe, 1 row, metal, 15 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 18 inches.
4-1589457-5	1589457	SSM015SC2DC036N	Dualobe, 1 row, metal, 15 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 36 inches thread for 1.0 jackscrews.
4-1589457-6	1589457	SSM015SC2DC048RN	Dualobe, 1 row, metal, 15 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 48 inches, clearance hole for 1.0 mounting screw, thread for 1.0 jackscrews.
4-1589457-7	1589457	SSM015SC2DX006N	Dualobe, 1 row, metal, 15 position, receptacle, 30 AWG 7 strand, white PTFE wire, 6 inches, thread for 1.0 jackscrews.
4-1589457-8	1589457	SSM015SC2DX012HN	Dualobe, 1 row, metal, 15 position, receptacle, 30 AWG 7 strand, white PTFE wire, 12 inches, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
5-1589457-0	1589457	SSM015SC2DX018N	Dualobe, 1 row, metal, 15 position, receptacle, 30 AWG 7 strand, white PTFE wire, 18 inches, thread for 1.0 jackscrews.
5-1589457-2	1589457	SSM015SC2DX024HN	Dualobe, 1 row, metal, 15 position, receptacle, 30 AWG 7 strand, white PTFE wire, 24 inches, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
5-1589457-3	1589457	SSM015SC2DY012N	Dualobe, 1 row, metal, 15 position, receptacle, 30 AWG 7 strand, white PTFE M16878/6 wire, 12 inches, thread for 1.0 jackscrews.
5-1589457-4	1589457	SSM015SC2DY018N	Dualobe, 1 row, metal, 15 position, receptacle, 30 AWG 7 strand, white PTFE M16878/6 wire, 18 inches, thread for 1.0 jackscrews.
5-1589457-5	1589457	SSM015SC4DX005N	Dualobe, 1 row, metal, 15 position, receptacle, 34 AWG 7 strand, white PTFE wire, 5 inches, thread for 1.0 jackscrews.
5-1589457-6	1589457	SSM025SC2DC012N	Dualobe, 1 row, metal, 25 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 12 inches, thread for 1.0 jackscrews.
5-1589457-7	1589457	SSM025SC2DC018	Dualobe, 1 row, metal, 25 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 18 inches.
5-1589457-8	1589457	SSM025SC2DC018R	Dualobe, 1 row, metal, 25 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 18 inches, clearance hole for 1.0 mounting screw.
5-1589457-9	1589457	SSM025SC2DC024N	Dualobe, 1 row, metal, 25 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 24 inches, thread for 1.0 jackscrews.
6-1589457-0	1589457	SSM025SC2DX006N	Dualobe, 1 row, metal, 25 position, receptacle, 30 AWG 7 strand, white PTFE wire, 6 inches, thread for 1.0 jackscrews.
6-1589457-1	1589457	SSM025SC2DX018N	Dualobe, 1 row, metal, 25 position, receptacle, 30 AWG 7 strand, white PTFE wire, 18 inches, thread for 1.0 jackscrews.
6-1589457-3	1589457	SSM025SC2DX024HN	Dualobe, 1 row, metal, 25 position, receptacle, 30 AWG 7 strand, white PTFE wire, 24 inches, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
6-1589457-4	1589457	SSM025SC3DY006N	Dualobe, 1 row, metal, 25 position, receptacle, 32 AWG 7 strand, white PTFE M16878/6 wire, 6 inches, thread for 1.0 jackscrews.
6-1589457-5	1589457	SSM037SC2DC018	Dualobe, 1 row, metal, 37 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 18 inches.
6-1589457-6	1589457	SSM037SC2DC018N	Dualobe, 1 row, metal, 37 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 18 inches, thread for 1.0 jackscrews.
6-1589457-7	1589457	SSM051SC2DC018	Dualobe, 1 row, metal, 51 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 18 inches.
6-1589457-8	1589457	SSM051SC2DC018N	Dualobe, 1 row, metal, 51 position, receptacle, 30 AWG 7 strand, color coded PTFE wire, 18 inches, thread for 1.0 jackscrews.
6-1589457-9	1589457	SSM051SC2DNC15Q	Dualobe, 1 row, metal, 51 position, receptacle, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 15 centimeters, 1.2 captive jackscrews.
7-1589457-1	1589457	SSM051SC2DT021	Dualobe, 1 row, metal, 51 position, receptacle, 30 AWG 7 strand, white ETFE M22759/33 wire, 21 inches.
7-1589457-3	1589457	SSM051SC2GX012N	Dualobe, 1 row, metal, 51 position, receptacle, 30 AWG 7 strand, FEP ribbon cable, 12 inches, thread for 1.0 jackscrews.

Sheet 2 of 2