

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **504618-2410**
Status: **Active**
Overview: SlimStack™ 0.35mm pitch Board-to-Board Connectors
Description: 0.35mm Pitch SlimStack™ SSB6 Board-to-Board Receptacle, Surface Mount, Dual Row, Vertical, 0.60mm Stacking Height, 2.00mm Width, 24 Circuits

Documents:

| | |
|---|---|
| Drawing (PDF) | Application Specification AS-504618-001 (PDF) |
| Product Specification PS-504618-001 (PDF) | RoHS Certificate of Compliance (PDF) |

General

| | |
|----------------|---|
| Product Family | PCB Receptacles |
| Series | 504618 |
| Application | Board-to-Board |
| Comments | PCB Retention via Solder Tab |
| Overview | SlimStack™ 0.35mm pitch Board-to-Board Connectors |
| Product Name | SlimStack™ |
| UPC | 887191620756 |

Physical

| | |
|--------------------------------|-----------------------|
| Circuits (Loaded) | 24 |
| Circuits (maximum) | 24 |
| Color - Resin | Black |
| Durability (mating cycles max) | 30 |
| Glow-Wire Compliant | No |
| Mated Height | 0.60mm |
| Material - Metal | Copper Alloy |
| Material - Plating Mating | Gold |
| Material - Plating Termination | Gold |
| Net Weight | 22.577/mg |
| Number of Rows | 2 |
| Orientation | Vertical |
| PCB Retention | Yes |
| Packaging Type | Embossed Tape on Reel |
| Pitch - Mating Interface | 0.35mm |
| Polarized to Mating Part | No |
| Polarized to PCB | No |
| Stackable | Yes |
| Temperature Range - Operating | -40°C to +85°C |
| Termination Interface: Style | Surface Mount |

Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 0.3A |
| Voltage - Maximum | 50V |

Material Info

Reference - Drawing Numbers

| | |
|---------------------------|------------------------------|
| Application Specification | AS-504618-001 |
| Product Specification | PS-504618-001 |
| Sales Drawing | SD-504618-001, SD-504618-002 |




image - Reference only

EU RoHS

**ELV and RoHS
Compliant**

**REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series
504618Series

Mates With
504622 0.35mm Pitch Sl...