

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [33472-1602](#)
Status: **Active**
Overview: [MX150™ Sealed and Unsealed Connector System](#)
Description: MX150™ Sealed Female Connector, Dual Row, 16 Circuits, Polarization B, without Connector Position Assurance, Light Gray

Documents:

3D Model	Application Specification AS-33472-100 (PDF)
Drawing (PDF)	Application Specification AS-33611-001 (PDF)
Product Specification PS-33472-000 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-34646-001 (PDF)	



image - Reference only

General

Product Family	Crimp Housings
Series	33472
Application	Power, Wire-to-Wire
Comments	No Connector Position Assurance (CPA)
More Detailed Tech Information	http://ewcap.uscarteams.org
Overview	MX150™ Sealed and Unsealed Connector System
Product Name	MX150™
UPC	756054493953

Physical

Circuits (maximum)	16
Circuits Detail	16
Color - Resin	Gray (Light), Natural
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene Alloy
Net Weight	18.020/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +125°C

Electrical

Current - Maximum per Contact	22A
-------------------------------	-----

Material Info

Old Part Number	CVP33472-1602
-----------------	---------------

Reference - Drawing Numbers

Application Specification	AS-33472-100, AS-33611-001
Product Specification	PS-33472-000, PS-34646-001
Sales Drawing	150-S-016-2-Z01, SD-33472-0001, SD-33472-0002

EU RoHS

ELV and RoHS Compliant
REACH SVHC
 Not Reviewed
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[33472Series](#)

Mates With

[33482](#) Male Dual Row Sealed Connector

Use With

[33012](#) MX150™ Female Terminal,
[34345-0001](#) MX150™ Cavity Plug Sealed