

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [16-02-0083](#)
Status: **Active**
Overview: C-Grid® Products
Description: SL™ Crimp Terminal 70058, 24-30 AWG, Reel Selective Gold (Au)

Documents:

[Drawing \(PDF\)](#) [Test Summary TS-70058-001 \(PDF\)](#)
[Product Specification PS-70058 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-70400 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	70058
Application	Signal
Crimp Quality Equipment	Yes
Overview	C-Grid® Products
Packaging Alternative	16-02-0098 (Loose)
Product Name	SL™
UPC	800753749139

Physical


Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.071/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	1.270µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.52mm max.
Wire Size AWG	24, 26, 28, 30
Wire Size mm²	N/A

Material Info

Old Part Number 70058-0008

Reference - Drawing Numbers

Product Specification	PS-70058, PS-70400
Sales Drawing	SD-70058-0008
Test Summary	TS-70058-001



EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[70058Series](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool For SL™ Crimp Terminals	0638258800
Insertion Tool	0011020022
T2 Terminator	0639103100
Tooling Die	
FineAdjust™ Applicator	0639001500
FineAdjust™ Applicator for Female Crimp Terminal, 24-30 AWG Wire	0639003100

Japan

Description	Product #
-------------	-----------

Applicator for M21 1A 0570143000
Bench Press, 22-30
AWG Wire
Hand Insertion Tool 0570336000

This document was generated on 12/23/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION