

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

19198-0013

Status:

Active

Overview:

Solderless Terminals

Description:

Avikrimp™ Spade Tongue Terminal for 16-14 AWG Wire, Stud Size 6 (M3.5), Mylar Tape Carrier, Length 20.45mm

Documents:

Drawing (PDF)

Product Specification PS-19902-011 (PDF)

Product Specification PS-19902-015 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR18689

UL

E32244

General

Product Family

Ring and Spade Terminals

Series

19198

Crimp Quality Equipment

Yes

Mil-Spec

N/A

Overview

Solderless Terminals

Product Name

Avikrimp™

Type

Spade

UPC

800753046047

Physical

Barrel Type

Closed

Flammability

94V-0

Insulation

Nylon (PA)

Material - Plating Mating

Tin

Net Weight

0.890/g

Packaging Type

Adhesive Tape on Reel

Plating min - Mating

2.540µm

Plating min - Termination

2.540µm

Stud Size

5-6 (M3-3.5)

Termination Interface: Style

Crimp or Compression

Wire Insulation Diameter

4.30mm max.

Wire Size AWG

14, 16

Wire Size mm²

1.00 - 2.50

Material Info

Old Part Number

BB-807-06T


Reference - Drawing Numbers

Product Specification

PS-19902-011, PS-19902-015

Sales Drawing

SD-19198-001



Series

image - Reference only

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19198Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Crimp Dies for MTA-100 Tape Applicator used in 3BF Press, MTA-105 Tape Applicator used in TM-2000™ Press, and ATP-301 Air Crimping Press for Mylar Tape Mounted Terminals Mini-Mac™ Applicator	0192880123
	0638850400

This document was generated on 12/11/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION