

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

19038-0001

Status:

Active

Overview:

Snap Plugs and Receptacles

Description:

InsulKrimp™ Snap Plug Receptacle, for 18-22 AWG Wire, PVC, Fits Male Plug Diameter 3.96mm

Documents:

Drawing (PDF)

Product Specification PS-19902-011 (PDF)

Product Specification PS-19902-013 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR18689

UL

E152602

General

Product Family

Quick Disconnects

Series

19038

Comments

Fits Male Plug size 3.96mm

Crimp Quality Equipment

Yes

Insulated

No

MolexKits

Yes

Overview

Snap Plugs and Receptacles

Product Name

InsulKrimp™

Type

Snap Receptacle

UPC

800753048621

Physical

Barrel Type

Closed

Color - Resin

Red

Flammability

94V-0

Gender

Female

Glow-Wire Compliant

No

Insulation

PVC

Lock to Mating Part

None

Material - Metal

Brass

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Material - Resin

PVC

Net Weight

1.041/g

Orientation

Straight

Packaging Type

Bag

Plating min - Mating

4.064µm

Plating min - Termination

4.064µm

Tab Thickness

N/A

Tab Width

N/A

Termination Interface: Style

Crimp or Compression

Wire Insulation Diameter

3.25mm max.

Wire Size AWG

18, 20, 22

Wire Size mm²

0.25 - 1.50

Electrical

Voltage - Maximum

600V

Material Info

Old Part Number

BRA-2156

Reference - Drawing Numbers



image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
19038Series

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool	0640012300
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640052300

This document was generated on 12/12/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION