

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [19071-0221](#)  
**Status:** **Active**  
**Overview:** Solderless Terminals  
**Description:** InsulKrimp™ Ring Tongue Terminal for 6 AWG Wire

**Documents:**

[Drawing \(PDF\)](#) [Product Specification PS-19902-013 \(PDF\)](#)  
[Product Specification PS-19902-009 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-19902-011 \(PDF\)](#)

**Agency Certification**

CSA LR18689  
 UL E32244

**General**

Product Family Ring and Spade Terminals  
 Series [19071](#)  
 Crimp Quality Equipment Yes  
 Mil-Spec N/A  
 Overview [Solderless Terminals](#)  
 Product Name InsulKrimp™  
 Type Ring  
 UPC 800753071827

**Physical**

Barrel Type Closed  
 Color - Resin Natural  
 Flammability 94V-0  
 Insulation PVC  
 Material - Plating Mating Tin  
 Net Weight 5.668/g  
 Packaging Type Bag  
 Stud Size 10 (M5)  
 Wire Insulation Diameter 11.20mm max.  
 Wire Size AWG 6

**Material Info**

Old Part Number E-660-10X

**Reference - Drawing Numbers**

Product Specification PS-19902-009, PS-19902-011, PS-19902-013  
 Sales Drawing SD-19071-015




image - Reference only

**EU RoHS**

**ELV and RoHS Compliant**

**REACH SVHC**

Not Reviewed

**Low-Halogen Status**

**Not Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

19071Series

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Hydraulic Dieless Crimping Tool	<a href="#">0638161700</a>
Hand Crimp Tool	<a href="#">0640013900</a>
Crimp Tool Kit for 6 AWG Insulated Ring Terminals	<a href="#">0640017770</a>
Die Set (large) for the HHLS Hydraulic Crimper	<a href="#">0192890004</a>
Manual Putt Pump Hydraulic System, Die set required	<a href="#">0192860117</a>

This document was generated on 01/14/2015

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**