

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** 19202-0063  
**Status:** Active  
**Overview:** Splices  
**Description:** Funnel Entry Butt Splice for 18-22 AWG Wire

**Documents:**  
[Drawing \(PDF\)](#)  
[Product Specification PS-19902-011 \(PDF\)](#)  
[Product Specification PS-19902-013 \(PDF\)](#)  
[RoHS Certificate of Compliance \(PDF\)](#)

**General**  
Product Family Splices  
Series 19202  
Crimp Quality Equipment Yes  
Mil-Spec N/A  
Overview Splices  
Product Name Butt - Funnel Entry  
UPC 800753048478

**Physical**  
Barrel Type Closed  
Color - Resin Red  
Insulation Nylon (PA)  
Material - Metal Copper  
Material - Plating Mating Tin  
Material - Plating Termination Tin  
Net Weight 0.962/g  
Packaging Type Carton  
Wire Insulation Diameter 3.73mm max. Funnel End, 4.10mm max.  
Wire Size AWG 18, 20, 22

**Material Info**  
Old Part Number A-945-DK

**Reference - Drawing Numbers**  
Product Specification PS-19902-011, PS-19902-013  
Sales Drawing SD-19202-002



Series  
image - Reference only

**EU RoHS**  
**ELV and RoHS**  
**Compliant**  
**REACH SVHC**  
Not Reviewed  
**Low-Halogen Status**  
**Not Reviewed**

**China RoHS**

**Need more information on product environmental compliance?**  
  
Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
For a multiple part number RoHS Certificate of Compliance, [click here](#)  
  
Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**  
19202Series

| Application Tooling   FAQ                                                                                                                                                       |            |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------|
| Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document. |            |
| Global                                                                                                                                                                          |            |
| Description                                                                                                                                                                     | Product #  |
| Crimp Head for the AT-200™ Pneumatic Hand Tool                                                                                                                                  | 0640050100 |
| PremiumGrade™ Hand Crimp Tool                                                                                                                                                   | 0640010100 |
| Crimp Head for the AT-200™ Pneumatic Hand Tool                                                                                                                                  | 0640050300 |
| Hand Crimp Tool                                                                                                                                                                 | 0640010300 |